



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 8

LOCTITE 5400

SDS No. : 596540  
V001.1

Revision: 05.07.2017

printing date: 05.02.2018

Replaces version from: 20.02.2017

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE 5400

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Adhesive

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### General chemical description:

Anaerobic adhesive

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

**SECTION 4: First aid measures**

**4.1. Description of first aid measures**

**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.

Obtain medical attention if irritation persists.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

**4.2. Most important symptoms and effects, both acute and delayed**

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

**SECTION 5: Firefighting measures**

**5.1. Extinguishing media**

**Suitable extinguishing media:**

Carbon dioxide, foam, powder

**Extinguishing media which must not be used for safety reasons:**

None known

**5.2. Special hazards arising from the substance or mixture**

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

**SECTION 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

Ensure adequate ventilation.

Avoid contact with skin and eyes.

Wear protective equipment.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

**6.4. Reference to other sections**

See advice in section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Use only in well-ventilated areas.

Avoid skin and eye contact.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

See advice in section 8

### Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

### 7.2. Conditions for safe storage, including any incompatibilities

Refer to Technical Data Sheet

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

### 7.3. Specific end use(s)

Adhesive

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Ethene, homopolymer 9002-88-4 [DUST, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Ethene, homopolymer 9002-88-4 [DUST, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL

**Occupational Exposure Limits**Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Ethene, homopolymer 9002-88-4 [DUSTS, NON-SPECIFIC, RESPIRABLE]		4	Time Weighted Average (TWA):		IR_OEL
Ethene, homopolymer 9002-88-4 [DUSTS, NON-SPECIFIC, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, TOTAL INHALABLE DUST]		6	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		IR_OEL

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**Engineering controls:  
Ensure good ventilation/extraction.Respiratory protection:  
Ensure adequate ventilation.  
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area  
Filter type: A (EN 14387)

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Wear protective glasses.

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	paste paste yellow orange
Odor	characteristic
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	> 93 °C (> 199.4 °F)
Flash point	> 93,3 °C (> 199.94 °F); no method
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	Not available.
Relative vapour density:	No data available / Not applicable
Density ( )	1,1 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Not miscible
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity (Cone and plate; Instrument: Haake cone and plate, RV1, C35/2°Ti; Shear gradient: 1 s-1)	30.000 - 70.000 mPa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Reaction with strong acids.  
Reacts with strong oxidants.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

No decomposition if used according to specifications.

### 10.5. Incompatible materials

See section reactivity.

### 10.6. Hazardous decomposition products

carbon oxides.  
nitrogen oxides  
Irritating organic vapours.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

#### General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

#### Oral toxicity:

This material is considered to have low toxicity if swallowed.

#### Inhalative toxicity:

Inhalation of vapors in high concentration may cause irritation of respiratory system

#### Skin irritation:

Although it is not a common sensitizer there may be a risk of sensitization on prolonged or repeated contact with damaged skin

#### Eye irritation:

May cause mild irritation to the eyes.

## SECTION 12: Ecological information

#### General ecological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.  
Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

### 12.1. Toxicity

**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

### 12.2. Persistence and degradability

**Persistence and Biodegradability:**

No data available.

### 12.3. Bioaccumulative potential / 12.4. Mobility in soil

**Mobility:**

Cured adhesives are immobile.

**Bioaccumulative potential:**

No data available.

### 12.5. Results of PBT and vPvB assessment

No data available.

### 12.6. Other adverse effects

No data available.

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Collection and delivery to recycling enterprise or other registered elimination institution.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Dispose of in accordance with local and national regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

### SECTION 14: Transport information

- 14.1. UN number**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**  
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**  
not applicable

### SECTION 15: Regulatory information

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %  
(2010/75/EC)

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

### SECTION 16: Other information

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**