



Supplier of Industrial and Consumer Batteries, Chargers, and Battery Packs

## JOIN OUR NEWSLETTER

SEARCH

BROWSE BY  
PRODUCT  
CATEGORY

BROWSE BY  
DEVICE  
MANUFACTURER

ADVANCED  
INDUSTRIAL  
SEARCH

[Home](#) / CUSTOM-47



*hover to zoom; click to enlarge*

### PART#: CUSTOM-47

**Chemistry:** Nickel Metal Hydride (NIMH)  
**Voltage:** 7.2  
**Capacity:** 750mAh  
**Measurements:** 1.7" x 0.9" x 1.2"  
 43.18mm x 22.86mm x 30.48mm

[Find a Distributor](#)

This replacement 3.6 Volt 1600 mAh Nickel Metal Hydride battery is used in the ITI - 34-051 Emergency Lighting and meets or exceeds original manufacturer specifications.

#### SPECIFICATIONS

Shipping Weight (oz)	2.7000
Manufacturer	Dantona
Warranty	6
UPC	728286210721
Length	1.7" (43.18mm)
Width	0.9" (22.86mm)
Height / Diameter	1.2" (30.48mm)
Voltage	7.2
mAh	750
Number of Cells	6
Battery Chemistry	Nickel Metal Hydride (NIMH)
Rechargeable	Rechargeable
Battery Color	Black
Qty Per Package	1
Type of Cell	AAA, Cylindrical
Weight	2.7 oz

#### Compatible Batteries and Devices

[Batteries \(5\)](#)  
[Devices \(1\)](#)



IMAGES ARE FOR REFERENCE ONLY! Please note that the capacity (mAh) may change without notice. Always consult the product specifications for correct information. Dantona Industries, Inc. is not affiliated in any way

**CAN'T FIND  
THE BATTERY  
YOU NEED?**

**CALL US AT  
1-800-Dantona  
TO SPEAK TO  
A BATTERY EXPERT**



**VIEW OUR WIDE  
SELECTION OF**

**Custom  
Battery  
Packs**

[SHOP OUR CUSTOM PACKS](#)