



T491, Tantalum, MnO2 Tantalum, 6.8 uF, 10%, 35 VDC, SMD, MnO2, Molded, 1.2 Ohms, 7343, Height Max = 3.1mm


CATHODE (-) END VIEW



SIDE VIEW




ANODE (+) END VIEW



Termination cutout  
 at KEMET's option,  
 either end.

BOTTOM VIEW



**Dimensions**

Dimensions	
Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.8mm +/-0.3mm
T	0.13mm REF
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
A	3.6mm MIN
B	0.5mm +/-0.15mm
E	3.5mm REF
G	3.5mm REF
P	0.9mm REF
R	1mm REF
X	0.1mm +/-0.1mm

**Packaging Specifications**

Weight:	446.84 mg
Packaging:	T&R, 178mm
Packaging Quantity:	500

**General Information**

Supplier:	KEMET
Series:	T491
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, MnO2, Molded
RoHS:	No
Prop 65:	<b>WARNING:</b> Cancer and reproductive harm - <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a> .
REACH:	SVHC (Pb – CAS 7439-92-1)
Termination:	Solder Coated
Shelf Life:	156 Weeks
MSL:	1

**Specifications**

Capacitance:	6.8 uF
Capacitance Tolerance:	10%
Voltage DC:	35 VDC (85C), 23.45 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	6.00% 120Hz 20C
Failure Rate:	N/A
Resistance:	1.2 Ohms (100kHz)
Ripple Current:	340 mAmps (100kHz 25C), 306 mAmps (85C), 136 mAmps (125C)
Leakage Current:	2.4 uA (5min 20C)