

ASMG-PT00-00001

1W Tri-color High Power LED

Datasheet

Description

The 1W Tri-Color High Power LED Light Source is a high performance energy efficient device which can handle high thermal and high driving current.

The low profile package design is suitable for a wide variety of applications especially where height is a constraint.

The package is compatible with reflow soldering process. This will give more freedom and flexibility to the light source designer.

Features


- Available in tri-color
- Energy efficient
- Compatible with reflow soldering process
- High current operation
- Long operation life
- Silicone encapsulation
- Moisture sensitivity level 1

Applications

- Sign backlight
- Retail display
- Commercial lighting
- Decorative lighting
- Architectural lighting

CAUTION This LED is Class 3B ESD sensitive per ANSI/ESDA/JEDEC JS-001. Please observe appropriate precautions during handling and processing. Refer to Application Note AN-1142 for additional details.

Package Dimensions



Notes:

1. All dimensions in millimeters (mm).
2. Tolerance is ± 0.20 mm unless otherwise specified.
3. Encapsulation = silicone.
4. Terminal finish = silver plating.
5. Thermal pad is connected to anode of Red.

Device Selection Guide ($T_J = 25^\circ\text{C}$, $I_F = 150\text{mA}$)

Part Number	Color	Luminous Flux, Φ_v (lm) ^{a, b}			Dice Technology
		Min	Typ	Max	
ASMG-PT00-00001	Red	25.0	28.0	35.0	AlInGaP
	Green	38.0	45.0	54.0	InGaN
	Blue	8.1	9.5	11.5	InGaN

a. Luminous flux is the total flux output as measured with an integrating sphere at a mono pulse condition.

b. Luminous flux tolerance = $\pm 10\%$.

Absolute Maximum Ratings

Parameter	Rating	Unit
DC Forward Current ^a	200	mA
Peak Forward Current ^b	250	mA
Reverse Voltage	Not designed for reverse bias	
LED Junction Temperature	120	$^\circ\text{C}$
Operating Temperature Range	-40 to +105	$^\circ\text{C}$
Storage Temperature Range	-40 to +120	$^\circ\text{C}$

a. Derate linearly as shown in Figure 7 and 8.

b. Duty factor = 10%, frequency = 1kHz.

Optical & Electrical Characteristics (T_J = 25°C)

Parameter	Min	Typ	Max	Unit	Test Conditions
Viewing Angle, 20½ ^a	-	155	-	Deg	I _F = 150mA
Forward Voltage, V _F ^b					
Red	1.8	2.2	2.8	V	I _F = 150mA
Green	2.8	3.1	3.7		
Blue	2.8	3.0	3.7		
Dominant Wavelength, λ _d ^c					
Red	620.0	623.0	630.0	nm	I _F = 150mA
Green	525.0	530.0	535.0		
Blue	455.0	458.0	460.0		
Peak Wavelength, λ _p					
Red	-	630.0	-	nm	I _F = 150mA
Green	-	522.0	-		
Blue	-	455.0	-		
Thermal Resistance, R _{θJ-S}					
Red	-	10	-	°C/W	LED junction to solder point
Green	-	20	-		
Blue	-	10	-		

a. 20½ is the off axis angle where the luminous intensity is half of the peak intensity.

b. Forward voltage tolerance = ±0.1V.

c. The dominant wavelength is derived from the CIE Chromaticity diagram and represents the perceived color of the device.

Part Numbering System

A S M G - P x1 0 0 - 0 x2 x3 x4 1

Code	Description	Option
x1	Color	T Tri-color
x2	Minimum flux bin (lm)	00 Red: 25.0 – 35.0lm
x3	Maximum flux bin (lm)	Green: 38.0 – 54.0lm
		Blue: 8.1 – 11.5lm
x4	Color bin	0 Full distribution

Bin Information

Flux Bin Limit (CAT)

Color	Bin	Luminous Flux (lm)	
		Min	Max
Red	-	25.0	35.0
Green	-	38.0	54.0
Blue	-	8.1	11.5

Tolerance = ±10%

Color bin Limit (BIN)

Color	Bin	Forward Voltage (V)	
		Min	Max
Red	4	620.0	630.0
Green	2	525.0	535.0
Blue	A	455.0	460.0

Tolerance = ±1.0nm

Example of bin information on reel and packaging label:

BIN: 42A → Red color bin 4
→ Green color bin 2
→ Blue color bin A

Figure 1 Relative luminous flux vs. forward current




Figure 2 Forward current vs. forward voltage




Figure 3 Dominant wavelength shift vs. forward current




Figure 4 Relative luminous flux vs. junction temperature




Figure 5 Forward voltage shift vs. junction temperature




Figure 6 Dominant wavelength shift vs. junction temperature




Figure 7 Derating curve according to solder point temperature (T_s)




Figure 8 Derating curve according to ambient temperature (T_A). Derated based on $T_{JMAX} = 120^\circ\text{C}$, $R\theta_{JA} = 50^\circ\text{C/W}$ for Red and Blue and $R\theta_{JA} = 60^\circ\text{C/W}$ for Green.




Figure 9 Pulse handling capability at $T_s \leq 105^\circ\text{C}$ for AlInGaP




Figure 10 Pulse handling capability at $T_s \leq 105^\circ\text{C}$ for InGaN




Figure 11 Radiation pattern for Red




Figure 12 Radiation pattern for Green




Figure 13 Radiation pattern for Blue




Figure 14 Spectral power distribution




Figure 15 Recommended soldering land pattern (mm)






Figure 16 Carrier tape dimensions



Notes:

1. Drawing not to scale.
2. All dimensions are in millimeters.
3. Tolerance is $\pm 0.10\text{mm}$ unless otherwise specified.

Figure 17 Reel dimensions




A	C	N	W2
178.0±1.0	13.1±0.5	60.0±0.5	16.2±0.5

Notes:

1. 500 pieces per reel.
2. Drawing not to scale.
3. All dimensions are in millimeters.

Soldering

Recommended reflow soldering condition:




- (a) Reflow soldering must not be done more than 2 times.
- (b) Do not apply any pressure or force on the LED during reflow and after reflow when the LED is still hot.
- (c) It is preferred to use reflow soldering to solder the LED. Hot plate shall only be used for rework if unavoidable but must be strictly controlled to conditions below:
 - LED temperature = 260°C max
 - Time at maximum temperature = 20sec max
- (d) User is advised to confirm beforehand whether the functionality and performance of the LED is affected by soldering with hot plate.
- (e) Hand soldering is not recommended.

Precautionary Notes

1. Handling precautions

The encapsulation material of the LED is made of silicone for better product reliability. Compared to epoxy encapsulant that is hard and brittle, silicone is softer and flexible. Special handling precautions need to be observed during assembly of silicone encapsulated LED products. Failure to comply might lead to damage and premature failure of the LED. Do refer to Application Note AN5288, Silicone Encapsulation for LED: Advantages and Handling Precautions for more information.

- (a) Do not poke sharp objects into the silicone encapsulant. Sharp object like tweezers or syringes might apply excessive force or even pierce through the silicone and induce failures to the LED die or wire bond.
- (f) Do not touch the silicone encapsulant. Uncontrolled force acting on the silicone encapsulant might result in excessive stress on the wire bond. The LED should only be held by the body.
- (f) Do not stack assembled PCBs together. Use an appropriate rack to hold the PCBs.
- (g) Surface of silicone material attracts dust and dirt easier than epoxy due to its surface tackiness. To remove foreign particles on the surface of silicone, a cotton bud can be used with isopropyl alcohol (IPA). During cleaning, rub the surface gently without putting much pressure on the silicone. Ultrasonic cleaning is not recommended.
- (h) For automated pick and place, Broadcom has tested nozzle size below to be working fine with this LED. However, due to the possibility of variations in other parameters such as pick and place machine maker/model and other settings of the machine, customer is recommended to verify the nozzle selected will not cause damage to the LED.



- (i) Storage
-The soldering terminals of these LEDs are silver plated. If the LEDs are being exposed in ambient environment for too long, the silver plating might be oxidized and thus affecting its solderability performance. As such, unused LEDs must be kept in sealed MBB with desiccant or in desiccator at <5%RH.

3. Application precautions


- (a) Drive current of the LED must not exceed the maximum allowable limit across temperature as stated in the datasheet. Constant current driving is recommended to ensure consistent performance.
- (b) LED is not intended for reverse bias. Do not use other appropriate components for such purpose. When driving the LED in matrix form, it is crucial to ensure that the reverse bias voltage is not exceeding the allowable limit of the LED.
- (c) Do not use the LED in the vicinity of material with sulfur content, in environment of high gaseous sulfur compound and corrosive elements. Examples of material that may contain sulfur are rubber gasket, RTV (room temperature vulcanizing) silicone rubber, rubber gloves etc. Prolonged exposure to such environment may affect the optical characteristics and product life.
- (d) Avoid rapid change in ambient temperature especially in high humidity environment as this will cause condensation on the LED.
- (e) If the LED is intended to be used in harsh or outdoor environment, the LED must be protected by means of protective cover against damages caused by rain water, dust, oil, corrosive gases, external mechanical stress etc.

4. Thermal management

Optical, electrical and reliability characteristics of LED are affected by temperature. The junction temperature (T_J) of the LED must be kept below allowable limit at all times. T_J can be calculated as below:

$$T_J = T_S + R_{\theta J-S} \times I_F \times V_{Fmax}$$

where T_S = LED solder point temperature as shown in illustration below [°C]
 $R_{\theta J-S}$ = Thermal resistance from junction to solder point [°C/W]
 I_F = Forward current [A]
 V_{Fmax} = Maximum forward voltage [V]



To measure the soldering point temperature, a thermocouple can be mounted on the T_S point as shown in illustration above. User is advised to verify the T_S of the LED in the final product to ensure that the LEDs are operated within all maximum ratings stated in the datasheet.

5. Eye Safety and Precautions

LEDs may pose optical hazards when in operation. It is not advisable to view directly at operating LEDs as it may be harmful to the eyes. For safety reasons, use appropriate shielding or personnel protection equipment.

DISCLAIMER: Broadcom's products and software are not specifically designed, manufactured or authorized for sale as parts, components or assemblies for the planning, construction, maintenance or direct operation of a nuclear facility or for use in medical devices or applications. Customer is solely responsible, and waives all rights to make claims against Broadcom or its suppliers, for all loss, damage, expense, or liability in connection with such use.

For product information and a complete list of distributors, please go to our web site:
www.broadcom.com



Broadcom, the pulse logo, Connecting everything, Avago Technologies, Avago, and the A logo are among the trademarks of Broadcom and/or its affiliates in the United States, certain other countries and/or the EU.

Copyright © 2016 by Broadcom. All Rights Reserved.

The term "Broadcom" refers to Broadcom Limited and/or its subsidiaries. For more information, please visit www.broadcom.com.

Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design.

Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.

29 November 2016

