DATASHEET - DC1-34046FB-A20CE1



Variable frequency drives; 3-/3-phase 400 V; 46 A; 22 kW; EMC filters; braking transistor

Powering Business Worldwide

DC1-34046FB-A20CE1 Part no.

185782 Catalog No.

Eaton Catalog No. DC1-34046FB-A20CE1

Technical data General

General			
Standards			Specification for general requirements: IEC/EN 61800-2 EMC requirements: IEC/EN 61800-3 Safety requirements: IEC/EN 61800-5-1
Certifications			CE, UL, cUL, RCM, Ukr SEPRO, EAC
Production quality			RoHS, ISO 9001
Climatic proofing	ρ_{W}	%	< 95%, average relative humidity (RH), non-condensing, non-corrosive
Ambient temperature			
operation (150 % overload)	8	°C	-10 - +50
Storage	9	°C	-40 - +60
Radio interference level			
Radio interference class (EMC)			C2, C3, depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.
Environment (EMC)			1st and 2nd environments as per EN 61800-3
maximum motor cable length	I	m	C2 ≤ 5 m C3 ≤ 25 m
Mounting position			Vertical
Altitude		m	0 - 1000 m above sea level Above 1000 m: 1% derating for every 100 m max. 4000 m
Degree of Protection			IP20/NEMA 0
Protection against direct contact			BGV A3 (VBG4, finger- and back-of-hand proof)
Main circuit			
Supply			
Rated operational voltage	U _e		400 V AC, 3-phase 480 V AC, 3-phase
Mains voltage (50/60Hz)	U_{LN}	V	380 (-10%) - 480 (+10%)
Input current (150% overload)	I _{LN}	Α	51.9
System configuration			AC supply systems with earthed center point
Supply frequency	f_{LN}	Hz	50/60
Frequency range	f_{LN}	Hz	48 - 62
Mains switch-on frequency			Maximum of one time every 30 seconds
Power section			
Function			Frequency inverter with internal DC link and IGBT inverter
Overload current (150% overload)	ΙL	Α	69
max. starting current (High Overload)	I _H	%	175
Note about max. starting current			for 3.75 seconds every 600 seconds
Output voltage with $V_{\rm e}$	U ₂		400 V AC, 3-phase 480 V AC, 3-phase
Output Frequency	f ₂	Hz	0 - 50/60 (max. 500)
Switching frequency	f_{PWM}	kHz	8 adjustable 4 - 24 (audible)
Operation Mode			U/f control Speed control with slip compensation sensorless vector control (SLV)
Frequency resolution (setpoint value)	Δf	Hz	0.1
Rated operational current			
At 150% overload	I _e	Α	46

Note			Rated operational current at an operating frequency of 16 kHz and an ambient a temperature of +50 $^{\circ}\text{C}$
Maximum leakage current to ground (PE) without motor	I _{PE}	mA	12.9
Fitted with			Radio interference suppression filter Brake chopper 7-digital display assembly
Frame size			FS4
tor feeder			
Note			for normal internally and externally ventilated 4 pole, three-phase asynchronou motors with 1500 rpm ⁻¹ at 50 Hz or 1800 min ⁻¹ at 60 Hz
Note			Overload cycle for 60 s every 600 s
Note			at 400 V, 50 Hz
150 % Overload	Р	kW	22
Note			at 440 - 480 V, 60 Hz
150 % Overload	P	НР	30
maximum permissible cable length	I	m	screened: 100 screened, with motor choke: 200 unscreened: 150 unscreened, with motor choke: 300
Apparent power			
Apparent power at rated operation 400 V	S	kVA	18.4
Apparent power at rated operation 480 V	S	kVA	22.08
Braking function			
DC braking torque			max. 100% of rated operational current \mathbf{I}_{e} , variable
minimum external braking resistance	R _{min}	Ω	22
Switch-on threshold for the braking transistor	U _{DC}	V	780 V DC
ntrol section			
erence voltage	U_s	V	10 V DC (max. 10 mA)
alog inputs			2, parameterizable, 0 - 10 V DC, 0/4 - 20 mA
alog outputs			1, parameterizable, 0 - 10 V
ital inputs			4, parameterizable, max. 30 V DC
ital outputs			1, parameterizable, 24 V DC
ay outputs			1, parameterizable, N/O, 6 A (250 V, AC-1) / 5 A (30 V, DC-1)
erface/field bus (built-in)			OP-Bus (RS485)/Modbus RTU, CANopen®
signed switching and protective elements			
ver Wiring			
IEC (Type B, gG), 150 %			FAZ-B63/3
150 % overload (CT/I _H , at 50 °C)			DX-LN3-060
tor feeder			
150 % overload (CT/I _H , at 50 °C)			DX-LM3-050
150 % overload (CT/I _H , at 50 °C)			DX-SIN3-048
% duty factor (DF)			DX-BR022-5K1

Design verification as per IEC/EN 61439

20 % duty factor (DF)

In	Α	46
P _{vid}	W	0
P _{vid}	W	801
P_{vs}	W	0
P _{diss}	W	0
	°C	-10
	°C	50
		Operation (with 150 % overload)
		Meets the product standard's requirements.
	P _{vid} P _{vid} P _{vs}	P _{vid} W P _{vid} W P _{vid} W P _{vs} W P _{diss} W °C

DX-BR022-9K2

10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Frequency converter =< 1 kV (EC001857) Electric engineering, automation, process control engineering / Electrical drive / Static frequency converter / Static frequency converter = < 1 kv (ecl@ss8.1-27-02-31-01 [AKE177011]) ٧ 380 - 480 Mains voltage Mains frequency 50/60 Hz Number of phases input 3 Number of phases output 3 Max. output frequency Hz 500 Max. output voltage ٧ 500 Rated output current I2N Α 46 kW Max. output at quadratic load at rated output voltage 22 Max. output at linear load at rated output voltage kW 22 With control unit Yes Yes Application in industrial area permitted Application in domestic- and commercial area permitted Yes Supporting protocol for TCP/IP No Supporting protocol for PROFIBUS No Supporting protocol for CAN Yes Supporting protocol for INTERBUS No Supporting protocol for ASI No Supporting protocol for KNX No Supporting protocol for MODBUS Yes Supporting protocol for Data-Highway No Supporting protocol for DeviceNet No Supporting protocol for SUCONET No Supporting protocol for LON No Supporting protocol for PROFINET IO No Supporting protocol for PROFINET CBA No Supporting protocol for SERCOS No Supporting protocol for Foundation Fieldbus No

	Yes
	No
	Yes
	0
	0
	0
	0
	1
	0
	0
	0
	0
	No
	Yes
	Yes
	No
	U converter
	IP20
mm	207
mm	168
mm	418
%	10
	mm mm

Approvals

Product Standards	UL 508C; CSA-C22.2 No. 14; IEC/EN61800-3; IEC/EN61800-5; CE marking
UL File No.	E172143
UL Category Control No.	NMMS, NMMS7
CSA File No.	UL report applies to both US and Canada
North America Certification	UL listed, certified by UL for use in Canada
Specially designed for North America	No
Suitable for	Branch circuits
Max. Voltage Rating	3~ 240 V AC IEC: TN-S UL/CSA: "Y" (Solidly Grounded Wey)
Degree of Protection	IEC: IP20

Dimensions

