

KEMET Part Number: LDECD3820KA0N00
(DECD3820KA0N00)

LDE, Film, Metallized PEN Stacked, Automotive Grade, 0.82 uF, 10%, 50 V, 40 VAC, 125C, 2220, 3.7mm



Dimensions	
Chip Size	2220
L	6mm +/-0.3mm
W	5mm +/-0.4mm
T	3.7mm MAX
B	0.5mm +0.5/-0.3mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	1750

General Information	
Supplier:	KEMET
Series:	LDE
Dielectric:	Metallized PEN Stacked
Style:	SMD Chip
Features:	Automotive Grade
RoHS:	Yes
Qualifications:	AEC-Q200
AEC-Q200:	Yes

Specifications	
Capacitance:	0.82 uF
Capacitance Tolerance:	10%
Voltage DC:	50 VDC
Voltage AC:	40 VAC
Temperature Range:	-55/+125C
Rated Temperature:	125C
Dissipation Factor:	0.8% 1kHz
Insulation Resistance:	487.8 MOhms
Max dV/dt:	100 V/us