

**KEMET Part Number: LDEED3470MA0N00**  
(DEED3470MA0N00)

LDE, Film, Metallized PEN Stacked, Automotive Grade, 0.47 uF, 20%, 100 V, 63 VAC, 125C, 2220, 4.4mm



Dimensions	
Chip Size	2220
L	6mm +/-0.3mm
W	5mm +/-0.4mm
T	4.4mm MAX
B	0.5mm +/-0.5/-0.3mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	1750

General Information	
Supplier:	KEMET
Series:	LDE
Dielectric:	Metallized PEN Stacked
Style:	SMD Chip
Features:	Automotive Grade
RoHS:	Yes
Qualifications:	AEC-Q200
AEC-Q200:	Yes

Specifications	
Capacitance:	0.47 uF
Capacitance Tolerance:	20%
Voltage DC:	100 VDC
Voltage AC:	63 VAC
Temperature Range:	-55/+125C
Rated Temperature:	125C
Dissipation Factor:	0.8% 1kHz
Insulation Resistance:	851.1 MOhms
Max dV/dt:	100 V/us