



G3 Flux Remover & Maintenance Cleaner 1631A-16S

Product Description

G3 Flux Remover & Maintenance Cleaner has a powerful spray and strong solvent that blasts off residues and cleans areas under components that a brush cannot touch. Patented defluxers formulated to be powerful and nonflammable, yet economical. Eliminates brushing and scrubbing, saving time and materials.

Features / Benefits

- Powerful Cleaner
- Non-flammable
- Non-ozone depleting
- Safe on electronics
- Rapid evaporation
- Zero residue
- Safe on most plastics

Usage Instructions

- For industrial use only.
- Read MSDS carefully prior to use

Disconnect equipment from power source. Hold can 6-8 inches away. When used as a general cleaner, start at top of area to be cleaned using a sweeping motion and spray the area, slowly working toward the bottom. To clean in hard to reach areas, insert extension tube in spray head. Allow components to dry completely before applying current.



Typical Product Data and Physical Properties

Physical state:	Liquid
Flash point:	Product does not sustain combustion
Flammable limits:	Lower 4.6% Upper 12.8%
Color:	Clear, colorless
Odor:	Ethereal
Boiling/condensation point	102.2°F (39°C)
Relative density:	1.22
Vapor pressure:	19.3 kPa (144.85 mmHg)
Volatility:	100% (w/w)
Heat of combustion:	0.84 kJ/g
Ignition distance:	0 cm
VOC:	64% by weight (EPA) 75% weight (CARB)
Shelf life:	5 years

G3 Flux Remover & Maintenance Cleaner 1631A-16S

Packaging and Availability

G3 Flux Remover & Maintenance Cleaner is available in the following sizes:

1631A-16S 368ml aerosol



Environmental Impact Data

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at www.techspray.com.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.