

KEMET Part Number: C1812C334MCRAC7800
(C1812C334MCRAC7800)

SMD Comm X7R HV, Ceramic, 0.33 uF, 20%, 500 VDC, X7R, SMD, MLCC, High Voltage, Temperature Stable, 1812



| Dimensions | |
|------------|-----------------|
| L | 4.5mm +/-0.3mm |
| W | 3.2mm +/-0.3mm |
| T | 2.1mm +/-0.20mm |
| B | 0.6mm +/-0.35mm |

| Packaging Specifications | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 500 |

| General Information | |
|-----------------------|--|
| Supplier: | KEMET |
| Series: | SMD Comm X7R HV |
| Style: | SMD Chip |
| Description: | SMD, MLCC, High Voltage, Temperature Stable |
| Features: | High Voltage |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |
| Chip Size: | 1812 |

| Specifications | |
|---|---------------------|
| Capacitance: | 0.33 uF |
| Capacitance Tolerance: | 20% |
| Voltage DC: | 500 VDC |
| Dielectric Withstanding Voltage: | 750 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | X7R |
| Dissipation Factor: | 2.50% 1kHz 25C |
| Aging Rate: | 3% Loss/Decade Hour |
| Insulation Resistance: | 303 MOhms |