

# HyperLink 2.4 GHz 17 dBi 90 Degree Sector Panel Wireless LAN Antenna Model: HG2417P-090 (Now ANATEL® APPROVED)

## **Applications and Features**

#### **Applications:**

- 2.4 GHz ISM Band
- IEEE 802.11b and 802.11g Wireless LAN
- Bluetooth<sup>®</sup>
- Public Wireless Hotspot
- WiFi
- Wireless Video Systems
- Wireless Internet Provider "cell" sites

#### Features:





- Superior performance
- All weather operation
- 90° beam-width
- 20° Down-Tilt Mounting Bracket
- Includes Mast Mounting Hardware
- Integral N-Female Connector
- RoHS Compliant



## **Superior Performance**

The HyperGain® HG2417P-090 Sector Panel WiFi Antenna combines high gain with a wide 90° beamwidth. It is a professional quality "cell site" antenna designed primarily for service providers in the 2.4GHz ISM band. Applications include IEEE 802.11b and 802.11g wireless LAN systems.

#### **ANATEL® APPROVED**

This antenna has been homologated (tested) in Brazil and is ANATEL® APPROVED for all installations in Brazil. This is another antenna in a series of L-com antennas certified for installation and use throughout Brazil.


### **Rugged and Weatherproof**

This antenna features a heavy-duty plastic radome for all-weather operation. The mounting system adjusts from 0 to 20 degrees down-tilt.

#### **Ideal for Wireless Internet "Cell" Sites**

This WiFi antenna is an ideal choice for Wireless Internet Provider "cell" sites since the cell size can be easily determined by adjusting the down-tilt angle. Horizontal coverage is a full 90 degrees.







## **Specifications**

## **Electrical Specifications**


Frequency	2400-2500 MHz
Gain	17 dBi
Horizontal Beam Width	90 degrees
Vertical Beam Width	6.5°
Impedance	50 Ohm
Max. Input Power	250 Watts
VSWR	< 1.3:1 avg.
Connector	N Female
Lightning Protection	DC Short


## **Mechanical Specifications**

10 lbs. ( 4.54 Kg)	
39 x 6 x 2.5 inches (99 x 15.3 x 6.4 cm)	
UV-Inhibited Polymer	
-40° C to 85° C (-40° F to 185° F)	
2 inch (5 cm) O.D. pipe max.	
Vertical	
0 to 20 degrees (adjustable)	
ANATEL® Brazil and RoHS	

## **Wind Loading Data**

Wind Loading	Front Surface	Side Surface
Area	1.63 sq. ft. (.15 sq. meters)	0.68 (.06 sq. meters)
@ 100 MPH (161 KPH)	74 lbs. (33.5 Kg)	35 lbs.(15.8 Kg)





# **Guaranteed Quality**

This product is backed by L-Com's Limited Warranty