

PX439N/GY

A thermally conductive flame retardant potting and encapsulating compound

Application

- Transformers
- PCB
- Control Modules
- General potting and encapsulation

Key Properties

- Non-toxic
- Low shrinkage
- High adhesion
- UL94 V-0 @ 3mm
- Good chemical and water resistance

Description

- Basic Two-component epoxy system
- Resin RX439N/GY
- Hardener HX439N/BK

| Physical Data (approx. – values) | Resin | Hardener | Mixed |
|----------------------------------|-------|----------|-----------|
| Colour | Grey | Black | Dark Grey |
| Specific Gravity | 2.09 | 0.94 | 1.93 |
| Viscosity (mPas) @ 25°C | 40000 | 110 | 7500 |

Cure Schedule (150ml sample)

| Temperature | Working Life (minutes) | Gel Time (minutes) | Light Handling (hours) | Full Cure (hours) |
|-------------|------------------------|--------------------|------------------------|-------------------|
| RT | 120 | 240 | 24 | 48 |
| 60°C | 20 | - | 4 | 8 |
| 80°C | - | - | 2 | 4 |

*RT is defined as 20-25°C

The above are typical values and will vary depending on the cured mass and application. Hotter temperatures may be used for faster cure but will result in higher post cure shrinkage and higher cure exotherm. Experimentation and testing is suggested to avoid side effects. For maximum properties a post cure may be required – Contact our technical service department for advice.

Processing

Mix ratio by weight 13.80:1
Mix ratio by volume 6.2:1

Typical Properties

| Test | Result | Unit |
|---------------------------------|------------------------------|---------------------------------------|
| Peak Exotherm (150ml @ RT) | 40 | °C |
| Shrinkage (Volume) | 0.3 | % |
| Thermal conductivity | 1.20 | W/mK |
| Thermal expansion | 35-45 | |
| Operating temperature range | -55 to +150 | °C (application & geometry dependent) |
| Dielectric strength | 18 | kV/mm |
| Volume Resistivity | 1×10^{12} | ohm.cm |
| Surface Resistivity | 1×10^{13} | ohm |
| Hardness | 85 | Shore D |
| Flame retardant | Approved (follow link below) | UL94 V-0 |
| Tensile strength | 65 | MPa |
| Compressive strength | 80 | MPa |
| Deflection Temperature | 100 | °C |
| Co-efficient of expansion | 35 - 45 | ppm/°C |
| Loss Tangent | 0.045 | @ 50 Hz |
| Permittivity | 4.99 | @ 50 Hz |
| Comparative tracking index | >850 | V (Method IEC 60112) |
| Water absorption (30 days @ RT) | 0.5 | % |
| Elongation at break | 1-3 | % |
| Flexural strength | 65 | MPa |
| Tg | 105-110 | °C |

| Approvals | |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| RoHS compliant | Yes |
| UL94 V-0 | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/showpage.html?name=OMFZ2_E76072&ccnshorttitle=Plastics+-+Component&objid=1073830268&cfqid=1073741824&version=versionless&parent_id=1073827222&sequence=1 |
| REACH (SVHC concentration) | 0% |

Packaging

PX439N is available in Bulk, Twinpacks, kits and sets

Availability

Available through distribution, www.resins-online.com and sales@robnor.co.uk

| Twinpack part numbers | |
|-----------------------|----------------|
| PX439N/GY/100 | PX439N/GY/500 |
| PX439N/GY/250 | PX439N/GY/1000 |
| | |

Twinpacks are pre-weighed resin and hardener components contained in a tough flexible film, separated by a removable clip and rail.

Once the clip and rail is removed the resin and hardener is thoroughly mixed within the bag and is immediately ready for use. Mixing will normally take ~ 3 minutes due to the viscosity; but pay special attention to the corners.

Twinpacks are ideal for small to medium production runs, prototyping and on-site or field use.

The twinpack weight/volume may also be tailored to a specific size on request.

For further details please visit www.robnor-resinlab.com

| Bulk Material part numbers | |
|----------------------------|----------------|
| RX439N/GY/5KG | HX439N/BK/1KG |
| RX439N/GY/10KG | HX439N/BK/5KG |
| RX439N/GY/25KG | HX439N/BK/10KG |
| | |

Both resin and hardener are supplied fully evacuated and ready for use.

Care should be taken to ensure when mixing the resins air is not entrained in the mixture.

If this is unavoidable the mixed resin and hardener should be re-evacuated before dispensing.

The bulk resin and hardener materials can be dispensed from suitable dispensing machinery, details provided by Fluid Research on request.

| Kits and Sets part numbers | |
|----------------------------|------------------|
| PX439N/GY/1KGKIT | PX439N/GY/2KGSET |
| PX439N/GY/10KGKIT | PX439N/GY/5KGSET |
| PX439N/GY/20KGKIT | |
| | |

Kits and Sets are provided in separate containers to the correct ratio.

In Kit form, pour the hardener into the larger resin container and use it as a mixing vessel.

Stir well using an appropriate mixer until homogeneous.

Note: Incomplete mixing will be characterised by erratic or partially incomplete cure even after extended time periods.

Cleaning

All equipment contaminated with mixed material should be cleaned before the material has hardened.

TS130 is a suitable non-flammable cleaning agent, although other solvents may be found suitable.

TS130 will also remove cured material provided it is allowed to soak for a number of hours.

Storage and Shelf Life

Material stored in the original unopened containers under cool dry condition between 15° and 25°C will have a shelf life of at least two years.

Once used the containers must be kept sealed to prevent effects from water, air or contaminants.

Health and Safety

Epoxy resin systems may cause sensitisation by skin contact or inhalation may be corrosive, harmful or toxic. It is therefore strongly recommended that skin and eye contact is avoided by the using of appropriate personal protective equipment such as gloves, safety glasses or goggles and overalls. Wash any contamination from the skin immediately and thoroughly and do not eat, smoke or drink in the working vicinity. Under normal working conditions a good source of ventilation is adequate, however if the material is heated, or where vapour levels are likely to exceed the occupational exposure limits appropriate respiratory protection must be worn. Local exhaust ventilation (LEV) may be required especially for curing ovens or where large volumes of material are curing. The above is given as a guide only; please refer to RX/HX439N Health and Safety data or our Technical Service Department for individual/specific advice.

Copyright & Warranty - Robnor Resinlab Limited

The results and information above does not constitute a specification and is given in good faith and without warranty. The information is derived from test/or extrapolations believed to be reliable and is quoted for guidance only. The product is offered for evaluation on the understanding the customer satisfies himself that the product is suitable for the intended application by proper evaluation and testing.

Contact Details

| | | |
|-------------------------|-------------|----------------------------------------------------------------------------|
| Robnor Resinlab Limited | Tel: | +44 (0) 1793 823741 |
| 31 Athena Avenue | Fax: | +44 (0) 1793 827033 |
| Elgin Industrial Estate | | |
| Swindon | Email: | support@robnor.co.uk |
| SN2 8EJ | Web: | www.robnor-resinlab.com |
| United Kingdom | Buy Online: | www.resins-online.com (UK only) |