

**KEMET Part Number: PME261KB5330KR30**  
(P561QE333K220A)

PME261/P561, Film, Metallized Paper, General Purpose, 0.033 uF, 10%, 400 VDC, 85C, Lead Spacing = 15.2mm



**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	PME261/P561
<b>Dielectric:</b>	Metallized Paper
<b>Style:</b>	Radial
<b>Features:</b>	Pulse in DC and low frequency applications
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Construction:</b>	Molded
<b>Miscellaneous:</b>	AC Operation: 70C MAX

**Dimensions**

<b>L</b>	18.5mm MAX
<b>H</b>	10.5mm MAX
<b>T</b>	5.2mm MAX
<b>S</b>	15.2mm +/-0.4mm
<b>LL</b>	30mm +5mm
<b>F</b>	0.8mm +/-0.05mm

**Specifications**

<b>Capacitance:</b>	0.033 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage AC:</b>	220 VAC
<b>Voltage DC:</b>	400 VDC
<b>Temperature Range:</b>	-40/+100C
<b>Rated Temperature:</b>	85C
<b>Dissipation Factor:</b>	1.3% 1kHz
<b>Insulation Resistance:</b>	12 GOhms
<b>Max dV/dt:</b>	1600 V/us

**Packaging Specifications**

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	500