

SAIP-M12BW-5-3.0V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com











Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration

Our developers have focused specifically on this issue and designed a host of different M8 and M12 sensor-actuator cables so you are bound to find the solution you need for your application.

The M8 and M12 sensor-actuator cables are supplied as standard with brass nickel-plated nuts. However if you are looking to use our products in an extremely harsh environment, we can also supply a variant with a plastic nut. This enables use in environments where cables with nickel-plated M8 and M12 nuts would rust.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Туре	SAIP-M12BW-5-3.0V
Order No.	<u>1466010300</u>
Version	Sensor/actuator line, One end without connector, M12, Number of poles: 5, 3 m, Socket, angled, Shielded: No, LED: No, Sheath material: PVC, Halogen: Yes
GTIN (EAN)	4050118275124
Qty.	1 pc(s).



SAIP-M12BW-5-3.0V

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com

Technical data

-			
Dim	ensions	and	weights

Net weight	160 g

Technical specifications for cable

5	Core cross-section	0.34 mm ²
$5.7 \pm 0.2 \text{ mm}$	Shielded	No
	Colour coding	brown, white, blue, black,
PVC		grey
PVC	Sheathing colour	Black
3 m	Temperature range, moving	-580 °C
-3080 °C	Halogen	Yes
No	Torsion resistance	0 °/m
No		
	5.7 ± 0.2 mm PVC PVC 3 m -3080 °C No	5.7 ± 0.2 mm Shielded Colour coding PVC PVC Sheathing colour 3 m Temperature range, moving Halogen No Torsion resistance

General technical data

Version	Socket, angled	connection thread	M12
Housing main material	PUR	Threaded ring material	Plastic
Coding	А	Protection degree	IP65, IP66, IP67, IP68, when screwed in
Contact surface	Gold-plated	LED	No
Rated voltage	125 V	Rated current	4 A
Insulation resistance	10 ⁸ Ω	Temperature range of housing	-25+85 °C
Tightening torque	M12: 0.8 - 1.2 Nm	Plugging cycles	≥ 100
Pollution severity	3	jumpered	No

Standards

Connector standard	IEC 61076-2-101	Certificate no. (cULus)	E307231

Classifications

ETIM 6.0	EC001855	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90	eClass 8.1	27-06-91-90
eClass 9.0	27-06-91-90	eClass 9.1	27-06-03-11

Approvals

Approvals



Downloads

Brochure/Catalogue	FL FIELDWIRING EN	
Engineering Data	EPLAN, WSCAD	



SAIP-M12BW-5-3.0V

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 16 D-32758 Detmold

Germany

Fon: +49 5231 14-0 Fax: +49 5231 14-292083 www.weidmueller.com


Drawings

Dimensioned drawing




Angled socket

Wiring diagram



Pole scheme



The ideal tool, the Screwty ® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F