

Brady B-2569 aqueous inkjet printable PET film with permanent adhesive

TDS No. B-2569

Effective Date: 10/31/2018

Description:

Brady B-2569 indoor marking film is an aqueous inkjet printable, flexible, matte finish, pressure sensitive adhesive product. B-2569 is designed to be used with the BradyJet™ J5000 Color Label Printer and BradyJet™ J2000 Color Label Printer.

Details:

Use:

Brady B-2569 is used indoors and outdoors for Pipe Markers, Arrow Tape, Warehouse Marking, Warning Panels, Safety Signs, Arc Flash and Visual Workplace labels.

Compliance Information: See www.bradyid.com or www.brady.eu for RoHS information.

Special Properties:

Aqueous inkjet printable polyester that yields full color and high resolution graphics.

Permanent acrylic pressure sensitive adhesive in B-2569 makes it applicable at cold temperatures.

Adhesive Type:

Acrylic

Substrate Type:

Polyester

Standard Material Colors:

White

Recommended Inks:

J5000: BradyJet™ J50 series ink cartridges; cyan, magenta, yellow, and black

J2000: BradyJet™ J20 series ink cartridge; cyan, magenta, and yellow

Thickness:

0.0045 in. (0.1143mm)

Adhesive Properties:

Adhesion to Stainless Steel

15 Minutes Dwell (Avg) 74 oz/in. (81N/100mm)

Ultimate Dwell (72 Hrs Avg) 74 oz/in. (81N/100mm)

Adhesion to Powder Coated Metal

15 Minutes Dwell (Avg) 48 oz/in(53 N/100mm)

Ultimate Dwell (72 Hrs Avg) 76 oz/in (83 N/100mm)

Adhesion to Polypropylene

15 Minutes Dwell (Avg) 72 oz/in (79 N/100mm)

Ultimate Dwell (72 Hrs Avg) 63 oz/in (69 N/100mm)

Adhesion to ABS

15 Minutes Dwell (Avg) 76 oz/in (83 N/100mm)

Ultimate Dwell (72 Hrs Avg) 76 oz/in (83 N/100mm)

Adhesion to Glass

15 Minutes Dwell (Avg) 76 oz/in (84 N/100mm)

Ultimate Dwell (72 Hrs Avg) 76 oz/in (84 N/100mm)

Note - B-2569 is not recommended for Bare concrete or Unpainted Wood

Abrasion Resistance (ASTM D4060):

CS 10 wheels, 250 g wts.

Print legible up to 500 cycles with J50 series pigment inks

Print legible up to 500 cycles with J20 series pigment inks

Note: same print settings as those used for chemical resistance (see below)

Gloss:

85 ° 8.4 Units

Minimum Application Temperature:

0°F (-18°C).

Service Temperature:

-40°F to 140°F (-40°C to 60°C).

Average Outdoor Durability:

J5000: Up to 1 year. (Average expected outdoor life of product will depend on user definition of failure, climatic conditions, mounting techniques, and printed color).

J2000: Up to 6 months. (Average expected outdoor life of product will depend on user definition of failure, climatic conditions, mounting techniques, and printed color).

Chemical Resistance:

Samples were printed using J50 series pigment inks with a BradyJet J5000 Color Label Printer by Brady recommended printer settings (Quality: Normal, Saturation: medium color + black). 100% Cyan(C), magenta(M), yellow(Y), and black (K) squares are printed for these tests.

Samples were printed using J20 series pigment inks with a BradyJet J2000 Color Label Printer by Brady recommended printer settings (Quality Mode: 3, Color Matching: best for graphics). 78% Cyan(C), magenta(M), yellow(Y), and process black (K) squares are printed for these tests.

Testing conducted at room temperature after equilibrating samples for 24 hours post printing.

REAGENT	J50 series ink cartridges		J20 series ink cartridges	
	7 DAY IMMERSION	RUB TEST	7 DAY IMMERSION	RUB TEST
Deionized Water	CMYK:NE	CMYK:NE	CMYK:NE	CMYK:NE
Windex® Commercial Line™ Original Glass Cleaner	CMYK:F1	CYMK:NE	CYMK:F1 MY: F2	CYMK:NE
10% HCl (pH 1)	CMYK:NE	CMYK:NE	CMYK:NE	CMYK:NE
10 wt% Sodium Chloride	CMYK:NE	CMYK:NE	CMYK:NE	CMYK:NE
10% NaOH (pH 14)	CMYK:F3	CMYK:NE*	CMYK:F3	CMYK:NE*
Isopropyl Alcohol	CMYK:NE	CYMK:F2	CMYK:NE	CYMK:F2
50 wt% ethanol	CMYK:NE	CMYK:F2	CMYK:NE	CMYK:F2
Gasoline	CMYK:NE	CMYK:F2	CMYK:NE	CMYK:F2

NE = No Effect on printed sample.

NE*= Reversible change. Coating turns yellow. Within 24hrs reverts back to original color. No ink removal.

F1= Fail – Coating turns blue. No ink removal.

F2= Fail – Some Ink removal.

F3= Fail – No Ink removal. Delamination.

7 Day Immersion: Immersed in reagent for 7 days.

Rub Test: 100 hand rubs over a minute with a Q-tips® Cotton Swab soaked in reagent by applying minimal pressure.

Shelf Life:

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual application.

Trademarks:

ASTM: American Society for Testing and Materials (U.S.A.)

Q-tips® Cotton Swabs is a registered trademark of Unilever

Windex® Commercial Line™ Original Glass Cleaner

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2018 Brady Worldwide, Inc. | All Rights Reserved

Material may not be reproduced or distributed in any form without written permission.