

29mm Bi-Metal Holesaw

Code	BS11
Diameter	29mm (1 1/8")
Cutting Depth	35mm
Cutting Edge	HSS M3
Tooth Pitch	4 / 6 tpi Variable Pitch
Mount	3/8"-20 UNF
Use With Arbor	Small Arbor - BA03 or BA04
Packaging	Cardboard Box
Pack Qty (Weight)	1 (78g)
Barcode	5039197009652



Description

Heavy Duty Holesaw for Industrial Use
HSS M3 Bi-Metal Cutting Edge provides Long Life
4/6tpi Variable Pitch Teeth enable Fast, Easy Cutting

Recommended Operating Speeds

Mild Steel - 300rpm Stainless - 150rpm Cast Iron - 200rpm
Brass - 400rpm Alu - 450rpm
Wood & Plastic - 2700rpm

Always use Cutting oil / spray when cutting metals

Applications

For cutting holes in Cast Iron, Stainless steel, steel, non-ferrous metals, wood and plastic.
Ideal for electrical, plumbing and production work

Suitable For

For use with all makes of mains powered and cordless rotary drills.