RF Between Series Adapters

BNC

Triaxial to BNC







Triaxial shell is shorted to outer shield

Triax





Model#	Туре
5299	3 Lug Triax (f)/BNC (m) adapter
5298	2 Lug Triax (f)/BNC (m) adapter
5090	BNC (f)/2 Lug Triax (m) adapter
5300	BNC (f)/3 Lug Triax (m) adapter

Triaxial: Body: tarnish resistant nickelplated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper; Outer Contact: gold-plated beryllium copper; Dielectric: PTFE.

BNC to TNC



Model#	Туре
3844	BNC (f)/TNC (m)

Rating: Maximum voltage for hands free use: 500 Vrms*, -85°F to + 325°F (-65°C to +165°C) (except as noted).

Impedance: 50Ω (except as noted).

BNC: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper (except as noted); Dielectric: PTFE.

BNC Female to Phono (RCA) Male



Model# 5319

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, 216°F (+102°C) max.

BNC: Center Contact: gold-plated.

UHF to BNC



3287

-	m 111	HHS	
Sal	man	MIE:	
	- 10	HERE'S	



3286

Model#	Туре	Special Features
3287	BNC (m)/ UHF (f)	Phos. Bronze Contact Nonconstant Impedance
3286	BNC (f)/UHF (m)	Nonconstant Impedance

Rating: Maximum voltage for hands free use: 335 Vrms*, -85 to +325°F (-65 to +165°C) (except as noted).

Impedance: 50Ω (except as noted).

UHF: Shell: tarnish resistant nickel-plated brass: Center Contact: male: gold-plated brass; female: goldplated beryllium copper (except as noted); Dielectric: PTFF

BNC Male to Phono Jack



Model# 4054

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max.

BNC Female to 1/4in (6.35mm) Phone Plug



Model# 1297

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max. Convert 2 conductor audio jacks to BNC.

Type N to BNC



 ← (37	1.46in 7.08mr	n) →
and the same	10	
minutes.	14	-
1		
	3288	

Model#	Туре	Special Features
3535	BNC (m)/N (f)	
3288	BNC (f)/N (m)	Beryllium Copper Male Contact

Rating: Maximum voltage for hands free use: 500 Vrms max., -85 to +325°F (-65 to +165°C) (except as noted).

Impedance: 50Ω (except as noted).

N: Shell: tarnish resistant nickel-plated brass; Center Contact: male: gold-plated brass; female: gold-plated beryllium copper (except as noted); Dielectric: PTFE.

BNC Female to Two Conductor, 0.14in (3.5mm) Dia. Mini Phone Plug



Model# 3837

Rating: Hands free testing in controlled voltage environment: 500 Vrms*, +257°F (+125°C) max. Convert 2 conductor audio jacks to BNC

www.pomonaelectronics.com