



## Main

|                               |                                      |
|-------------------------------|--------------------------------------|
| Range of product              | Harmony XB5                          |
| Product or component type     | Head for illuminated selector switch |
| Product compatibility         | Integral LED                         |
| Device short name             | ZB5                                  |
| Bezel material                | Plastic                              |
| Mounting diameter             | 1.18 in (30 mm)                      |
| Head type                     | Built-in-flush                       |
| Sale per indivisible quantity | 1                                    |
| Shape of signaling unit head  | Round                                |
| Type of operator              | Spring return to centre              |
| Operator profile              | Blue standard handle                 |
| Operator position information | 3 positions +/- 45°                  |

## Complementary

|                             |   |
|-----------------------------|---|
| CAD overall width           | 1.46 in (37 mm)   |
| CAD overall height          | 1.46 in (37 mm)   |
| CAD overall depth           | 1.81 in (46 mm)   |
| Product weight              | 0.07 lb(US) (0.03 kg)   |
| Mechanical durability       | 1000000 cycles  |
| Electrical composition code | M10 <= 2 contacts using single blocks in front mounting with integral LED<br>M6 <= 2 contacts using single blocks in front mounting with integral LED and transformer<br>MF1 <= 2 contacts using single blocks in front mounting with integral LED<br>M3 <= 4 contacts using single blocks in front mounting with integral LED<br>M4 <= 4 contacts using single and double blocks in front mounting with integral LED |

## Environment

|                      |    |
|----------------------|----|
| Protective treatment | TH |
|----------------------|----|

|                                       |  |
|---------------------------------------|--|
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)   |
| Ambient air temperature for operation | -40...158 °F (-40...70 °C)   |
| Overvoltage category                  | Class II conforming to IEC 60536   |
| IP degree of protection               | IP69<br>IP67<br>IP66 conforming to IEC 60529<br>IP69K  |
| NEMA degree of protection             | NEMA 13<br>NEMA 4X   |
| Resistance to high pressure washer    | 1015.26 psi (7000000 Pa) at 131 °F (55 °C), distance: 0.1 m  |
| IK degree of protection               | IK03 conforming to IEC 50102   |
| Standards                             | JIS C 4520<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>UL 508<br>EN/IEC 60947-1<br>CSA C22.2 No 14<br>EN/IEC 60947-5-5  |
| Product certifications                | DNV<br>CSA<br>UL listed<br>RINA<br>BV<br>GL<br>LROS (Lloyds register of shipping)  |
| Vibration resistance                  | 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6  |
| Shock resistance                      | 30 gn (duration = 18 ms) half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) half sine wave acceleration conforming to IEC 60068-2-27 |

## Ordering and shipping details

|                       |                                       |
|-----------------------|---------------------------------------|
| Category              | 22467 - PUSHBUTTONS,22MM(PLASTIC) NEW |
| Discount Schedule     | CS2                                   |
| Nbr. of units in pkg. | 1                                     |
| Package weight(Lbs)   | 5.0000000000000003E-2                 |
| Returnability         | N                                     |
| Country of origin     | FR                                    |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1804 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available   |
| Product end of life instructions | Available   |
| California proposition 65        | WARNING: This product can expose you to chemicals including:  |
| ----- Substance 1                | Nickel compounds, which is known to the State of California to cause cancer, and  |
| ----- Substance 2                | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.            |
| ----- More information           | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>   |