muRata Capacitor Data Sheet GRM0335C2A1R1WA01# "#" indicates a package specification code.

In Production General 125 Cmax. Reflow ROHS REACH

< List of part numbers with package codes >

Shape

GRM0335C2A1R1WA01D , GRM0335C2A1R1WA01W , GRM0335C2A1R1WA01J

Shape		
L size	0.6 ±0.03mm	
W size	0.3 ±0.03mm	
T size	0.3 ±0.03mm	
External terminal width e	0.1 to 0.2mm	
Distance between external terminals g	0.2mm min.	
Size code in inch(mm)	0201 (0603M)	

Packaging	Specifications	Minimum quantity
D	φ180mm Paper taping	15000
J	φ330mm Paper taping	50000
W	φ180mm Paper taping (W8P1*) * Width : 8mm, Pocket pitch : 1mm	30000

References

E

Mass (typ.)	
1 piece	0.33mg
φ180mm Reel	118g

Specifications


Capacitance	1.1pF ±0.05pF
Rated voltage	100Vdc
Temperature characteristics (complied standard)	C0G(EIA)
Temperature coefficient	0±30ppm/°C
Temperature range of temperature characteristics	25 to 125°C
Operating temperature range	-55 to 125°C

🔔 Attention

This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

muRata Murata Manufacturing Co., Ltd.

Chart of characteristic data (The charts below may show another part number which shares its characteristics.)



2 of 2

🔔 Attention

 This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.