




Pushing Performance

Han-Eco 24B-HSM2-with SL-M40



| | |
|--------------------|---|
| Part number | 19 43 024 0293 |
| Specification | Han-Eco 24B-HSM2-with SL-M40 |
| HARTING eCatalogue | https://b2b.harting.com/19430240293 |

Identification

| | |
|--------------------------|-------------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-Eco® B |
| Type of hood/housing | Surface mounted housing |

Version

| | |
|--------------|----------------------|
| Locking type | Single locking lever |
| Size | 24 B |
| Version | Side entry |
| Cable entry | 2x M40 |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Number of relockings | ≥500 |
| Degree of protection acc. to IEC 60529 | IP66 |

Material properties

| | |
|--|-------------------------------------|
| Material (hood/housing) | Polyamide Fibre-glass reinforced |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (seal) | NBR |
| Colour (seal) | RAL 9005 (jet black) |
| Material (locking) | Polyamide Fibre-glass reinforced |
| Colour (locking) | RAL 9005 (jet black) |
| Material flammability class acc. to UL 94 | V-0 |
| Material flammability class acc. to UL 94 (locking levers) | V-0 |

Specifications and approvals

| | |
|----------------|--|
| Specifications | IEC 61984 EN 45545-2 R22: HL1, HL2, HL3 |
|----------------|--|



Pushing Performance

Specifications and approvals

| | |
|--|-------------------------------|
| | EN 45545-2 R23: HL1, HL2, HL3 |
| | EN 45545-2 R24: HL1, HL2, HL3 |

Commercial data

| | |
|--------------------------------|----------|
| Packaging size | 1 |
| Country of origin | Germany |
| European customs tariff number | 85389099 |