

**Part Number: 8720NH**

Control Cable, 14 AWG, 19 x 27, 600V, LSNH



## Product Description

14 AWG , 19 x 27, Stranded TC Conductors, 1 Pair, LSNH

## Technical Specifications

### Product Overview

Environmental Space:	Indoor
Suitable Applications:	Audio, signal, control and instrumentation applications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
14	Stranded	TC - Tinned Copper	1

Conductor Count:	2
Conductor Size:	14 AWG

#### Insulation

Material	Nominal Diameter	Diameter +/- Tolerance
PO - Polyolefin	3.55 mm	0.8 mm

#### Color Chart

Number	Color
Wire 1	Black
Wire 2	Clear

#### Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG
Foil	1	Aluminum/Polyester	Beldfoil® (Z-Fold®)	100 %	Stranded tinned copper	AWG 16/19

#### Outer Jacket Material

Material	Color	Nominal Diameter	Nominal Wall Thickness
LSZH / FRNC	Grey	9 mm	0.9 mm

## Construction and Dimensions

### Cabling

Description
2 wires stranded + drainwire stranded tinned copper AWG16/19

## Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
8.3 Ohm/km	11.3 Ohm/km

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
78 pF/m	154 pF/m

Shielding:	Foil(s) or Copper Tape(s)
------------	---------------------------

#### Impedance

Nominal Characteristic Impedance
58 Ohm

#### Current

Max. Recommended Current [A]
9.5 A

#### Temperature Range

Storage Temp Range:	-30°C To +80°C
Operating Temp Range:	-30°C To +70°C
Other Temp Range:	-20-+80 °C

#### Mechanical Characteristics

Min Bend Radius (W/o Pulling Strength):	45 mm
Min Setting Radius:	90 mm

#### Standards

UL AWM Style:	UL AWM 21310
---------------	--------------

#### Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2014-11-14
---------------------------------------	------------

#### Suitability

Suitability - Non-Halogenated:	IEC 60754-2
--------------------------------	-------------

#### Flammability, LSOH, Toxicity Testing

UL Flammability:	UL horizontal flame test
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

#### Part Number

#### Variants

Item #	Color
8720NH.00500	Gray

#### History

Revision Number:	1
------------------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.