



T495, Tantalum, MnO2 Tantalum, 10 uF, 20%, 10 VDC, SMD, MnO2, Molded, Low ESR, 2 Ohms, 3216, Height Max = 1.8mm


CATHODE (-) END VIEW



SIDE VIEW




ANODE (+) END VIEW



Termination cutout at KEMET's option, either end.

BOTTOM VIEW



General Information

Supplier:	KEMET
Series:	T495
Dielectric:	MnO2 Tantalum
Style:	SMD Chip
Description:	SMD, MnO2, Molded, Low ESR
Features:	Low ESR
RoHS:	Yes
Termination:	Tin
Shelf Life:	156 Weeks
MSL:	1

Dimensions

Footprint	3216
L	3.2mm +/-0.2mm
W	1.6mm +/-0.2mm
H	1.6mm +/-0.2mm
T	0.13mm REF
S	0.8mm +0.2/-0.3mm
F	1.2mm +/-0.1mm
A	1.2mm MIN
B	0.4mm +/-0.15mm
E	1.3mm REF
G	1.1mm REF
P	0.4mm REF
R	0.4mm REF
X	0.1mm +/-0.1mm

Specifications

Capacitance:	10 uF
Capacitance Tolerance:	20%
Voltage DC:	10 VDC (85C), 6.7 VDC (125C)
Temperature Range:	-55/+125C
Rated Temperature:	85C
Dissipation Factor:	6.00% 120Hz 20C
Failure Rate:	N/A
Resistance:	2000 mOhms (100kHz)
Ripple Current:	194 mAmps (100kHz 25C), 174.6 mAmps (85C), 77.6 mAmps (125C)
Leakage Current:	1 uA (5min 20C)

Packaging Specifications

Weight:	58.6 mg
Packaging:	T&R, 178mm
Packaging Quantity:	2000