

**KEMET Part Number: C1210C475M4VACTU**  
(C1210C475M4VAC7800)

SMD Comm Y5V, Ceramic, 4.7 uF, 20%, 16 VDC, Y5V, SMD, MLCC, General Purpose, Class III, 1210



**Dimensions**

<b>L</b>	3.2mm +/-0.2mm
<b>W</b>	2.5mm +/-0.2mm
<b>T</b>	1.9mm +/-0.20mm
<b>B</b>	0.5mm +/-0.25mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	2000

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	SMD Comm Y5V
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, General Purpose, Class III
<b>Features:</b>	Class III
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Miscellaneous:</b>	Note: Referee time for Y5V dielectric for this part number is 48 hours
<b>Chip Size:</b>	1210

**Specifications**

<b>Capacitance:</b>	4.7 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	16 VDC
<b>Dielectric Withstanding Voltage:</b>	40 V
<b>Temperature Range:</b>	-30/+85C
<b>Temperature Coefficient:</b>	Y5V
<b>Dissipation Factor:</b>	7.00% 120Hz 25C
<b>Aging Rate:</b>	7% Loss/Decade Hour
<b>Insulation Resistance:</b>	21 MOhms