

# 9080GCB05

## Thermal-Magnetic Overcurrent Circuit Protector Track Mount 250VAC/65VDC 0.5AMP

Product availability : Stock - Normally stocked in distribution facility



Price\* : 66.00 USD



### Main

Range of product	9080GCB
Product or component type	Circuit Protector
Trip Unit Type	Thermal-magnetic
Electrical Connection	Box lugs

### Complementary

Protection type	Overcurrent
Contact operation	Trip-free
Device application	Industrial application
Line Rated Current	0.5 A
Number of Poles	1P
System Voltage	250 V AC 65 V DC
Wire Size	AWG 16...AWG 10 (copper)
Wire stripping length	0.5 in
Terminal Tightening Torque	7 lbf.in control circuit cage type connector
Terminal Rating	Factory wiring only
Operating Temperature	-22...140 °F
Calibration Temperature	70 °F
Mounting support	35 mm DIN rail 9080GH track
Height	3.45 in
Width	3.15 in
Depth	0.5 in

## Environment

Product certifications	CE UL recognized E233026 CCN QVNU2 CSA file 025490 class 3211 07
Standards	UL 1077 DIN 57470 CSA C22.2 No 235

## Ordering and shipping details

Category	21703 - 9080 GCB
Discount Schedule	CP5
GTIN	00785901481102
Nbr. of units in pkg.	1
Package weight(Lbs)	0.16
Returnability	Y
Country of origin	DE

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0934 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------