

Accessories
ZQV 4/5 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

General ordering data

| | |
|------------|------------------------------------|
| Type | ZQV 4/5 GE |
| Order No. | 1608980000 |
| Version | Accessories, Cross-connector, 32 A |
| GTIN (EAN) | 4008190263256 |
| Qty. | 20 pc(s). |

**Accessories
ZQV 4/5 GE**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Width | 2.8 mm | Width (inches) | 0.11 inch |
| Height | 28.8 mm | Height (inches) | 1.134 inch |
| Depth | 31.6 mm | Depth (inches) | 1.244 inch |
| Net weight | 4.25 g | | |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |
|----------------------------------|--------|----------------------------------|--------|

Material data

| | | | |
|---------------------------|-------|-------------|--------|
| Material | Wemid | Colour code | yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|---------|-------------------|------|------|
| Version | For the terminals | Rail | none |
|---------|-------------------|------|------|

Additional technical data

| | | | |
|--------------------------|---------|---------------------|-----------------|
| Explosion-tested version | Yes | Installation advice | Direct mounting |
| Type of fixing | Plugged | | |

Dimensions

| | |
|-----------------|--------|
| Pitch in mm (P) | 6.1 mm |
|-----------------|--------|

Rating data

| | |
|---------------|------|
| Rated current | 32 A |
|---------------|------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000489 | ETIM 4.0 | EC000489 |
| ETIM 5.0 | EC000489 | ETIM 6.0 | EC000489 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-14-11-40 |
| eClass 6.2 | 27-14-11-40 | eClass 7.1 | 27-14-11-40 |
| eClass 8.1 | 27-14-11-40 | eClass 9.0 | 27-14-11-40 |
| eClass 9.1 | 27-14-11-40 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |
| User Documentation | Operating instructions_ZDU1.5-ZDU35_ZQV.pdf |