

APEX[®] MIXED SERIES



APEX[®] Mixed
14W Male & Female

APEX[®] FAMILY BENEFITS

- Heavy-duty performance
- Highest current rating
- Ergonomic design

MIXED SERIES FEATURES

- APEX 150 and APEX 2.8 terminals for power and signal delivery
- Compliant with USCAR design guidelines and performance standards
- Primary Lock Retainer (PLR)
- Shorting Bar version available for safety circuit protection (where electro-static discharge must be prevented)



AVAILABLE CONFIGURATIONS

Cavity Count (ways)	14
Cavity Configurations	1.5 mm & 2.8 mm
Genders	Male & Female
Sealing Type	Mat seal
CPA	Optional




APPLICATIONS

Sealed inline applications

See back page for representative part numbers and packaging dimensions.



TEMPERATURE



VIBRATION



ENVIRONMENTAL PROTECTION



About Aptiv

Aptiv is a global technology company that develops safer, greener and more connected solutions enabling the future of mobility. Headquartered in Dublin, Aptiv has approximately 150,000 employees and operates 14 technical centers, as well as manufacturing sites and customer support centers in 45 countries.

Visit aptiv.com



Cavity count	Blade size (mm)	Gender	Dimensions W x H x D (mm)	Part number	Index	Color	Indexes offered
14	1.5 / 2.8	F	38.3 x 25.1 x 37.9	13878050	A	Black	B, C, D, E, F
14	1.5 / 2.8	M	36.2 x 23.3 x 61.5	13694022	A	Black	B, C, D, E, F

Please, refer to the APEX® catalogue for the full part number list.


DIMENSION MEASUREMENT SAMPLE



APEX® Mixed
14W Female assembly

APEX® Mixed
14W Male assembly

EXPLODED VIEW



APEX® Mixed
14W Female

APEX® Mixed
14W Male

COMPATIBLE WITH



Part numbers, specifications, dimensions and performance data in this document are for general references only and are subject to change without notice. To verify product information, please contact an Aptiv representative.

CS-SP41-APEX-En0718