


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0309681060**
Status: **Active**
Overview: H-DAC 64™ Dual-Row High Density Automotive Connectors
Description: 2.54mm Pitch, 0.64mm Width H-DAC 64 High Density Automotive Crimp Housing, Dual Row, 6 Circuits, Polarization Option #1, Gray

Documents:

| | |
|---|--|
| 3D Model | Application Specification AS-30700-000-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-30907-760 (PDF) |
| Product Specification PS-30968-0001-001 (PDF) | RoHS Certificate of Compliance (PDF) |



General

| | |
|----------------|---|
| Product Family | Crimp Housings |
| Series | 30968 |
| Application | Power, Wire-to-Wire |
| Comments | Polarization Option #1, Polarization Option #1 |
| Overview | H-DAC 64™ Dual-Row High Density Automotive Connectors |
| Product Name | H-DAC 64 |
| UPC | 800754879798 |

Physical

| | |
|-------------------------------|----------------------|
| Circuits (maximum) | 6 |
| Color - Resin | Gray |
| Gender | Plug |
| Glow-Wire Capable | No |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Resin | Modified Polystyrene |
| Net Weight | 4.167/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 2.54mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +100°C |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 7.0A |
|-------------------------------|------|

Solder Process Data

| | |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|-------------------|
| Application Specification | AS-30700-000-001 |
| Packaging Specification | PK-30907-760 |
| Product Specification | PS-30968-0001-001 |
| Sales Drawing | SD-30968-120 |

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

[30968](#) Series

Mates With

[30700](#) , [31389](#) H-DAC 64 High Density Automotive Connectors

Use With

Contact Molex for Terminal information.