

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0350539002**
Status: **Active**
Description: 2.50mm Pitch Wire-to-Wire Terminal, Male, 22-28 AWG (0.33-0.81mm²), Tin-plated, Reel, for 35184 Housing

Documents:

Drawing (PDF)	Product Specification PS-35531-001-001 (PDF)
Product Specification PS-35053-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-35184-001-001 (PDF)	

General

Product Family	Crimp Terminals
Series	<u>35053</u>
Application	Signal
Crimp Quality Equipment	Yes
Product Name	N/A
UPC	800754253345

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.073/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.15-1.90mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm ²	N/A


Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-35053-001-001, PS-35184-001-001, PS-35531-001-001
Sales Drawing	SD-35053-9002



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

35053 Series

Mates With

5103 Crimp Terminal

Use With

35184

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction and Activation Tool	638132700
Hand Crimp Tool	638190800
FineAdjust Applicator for 2.50mm Wire-to-Wire Male Crimp Terminal, 22-28 AWG Wire	639007900

T2 Terminator 639107900
Tooling Die for Wire-
to-Wire Male Crimp
Terminal, 22-28
AWG

This document was generated on 04/16/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION