

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643241039](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: 2.80mm, CMC CP Female Terminal, Tin plated, for Tab Dimensions 2.8mm x 0.8mm , Wire Size > 1mm² - 2mm²

Documents:

3D Model	Application Specification AS-64324-001-FR-001 (PDF)
Drawing (PDF)	Application Specification AS-98420-001-001 (PDF)
Product Specification PS-64326-001-001 (PDF)	Application Specification AS-98420-001-CH-001 (PDF)
Application Specification AS-64318-002-001 (PDF)	Application Specification AS-98420-001-FR-001 (PDF)
Application Specification AS-64318-002-CH-001 (PDF)	Application Specification AS-98420-001-SP-001 (PDF)
Application Specification AS-64318-002-FR-001 (PDF)	Packaging Specification 313025040-000 (PDF)
Application Specification AS-64318-002-SP-001 (PDF)	Packaging Specification PK-98910-001-001 (PDF)
Application Specification AS-64324-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-64324-001-CH-001 (PDF)	

General

Product Family	Crimp Terminals
Series	64324
Application	Power, Wire-to-Wire
Comments	* Current tested on a fully loaded connector, current for temperature increase of 40°C. Current max = 21A for 2.80mm Terminal (5.00mm ² wire), * Current tested on a fully loaded connector, current for temperature increase of 40°C. Current max = 21A for 2.80mm Terminal (5.00mm ² wire)
Crimp Quality Equipment	Yes
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC, CP Terminal
UPC	883906128418


Physical

Gender	Female
Material - Metal	High Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.687/g
Packaging Type	Reel
Plating min - Mating	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.10mm-2.80mm
Wire Size AWG	14, 16
Wire Size mm ²	> 1.00-2.00

Electrical

Current - Maximum per Contact	21.0A
Voltage - Maximum	14V DC

Solder Process Data



EU ELV

Compliant

EU RoHS

Not Reviewed

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Relevant

Compliant

Not Contained

Search Parts in this Series

[64324 Series](#)

Mates With

CMC Connector [64318](#) , [64321](#) , [64326](#) , [643251175](#)

Use With

CMC Connector [64318](#) , [64321](#) , [64326](#) , [643251175](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp
Tool for CP 2.8
Receptacle 14-16
AWG Type TXL Wire
and>1.00-2.00mm²
Type ID & ID Wire
with 2.80mm,

[638119700](#)

Lead-free Process Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

AS-64318-002-001, AS-64318-002-CH-001,
AS-64318-002-FR-001, AS-64318-002-SP-001,
AS-64324-001-001, AS-64324-001-CH-001,
AS-64324-001-FR-001, AS-98420-001-001,
AS-98420-001-CH-001, AS-98420-001-FR-001,
AS-98420-001-SP-001

Crimp Specification

CS-64324-001

Packaging Specification

313025040-000, PK-98910-001-001

Product Specification

PS-64326-001-001

Sales Drawing

SD-64324-001-001

CMC Wire Seal

Receptacle

Extraction Tool [638132500](#)

Hand Crimp Tool for [638234200](#)

CP 2.8 Receptacle

Crimp Terminals

Mini-Mac Applicator [638951100](#)

for CP2.8 Terminals,

>1.00-2.00mm² ID &

IR Wire

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION