

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0016020083](#)
Status: **Active**
Overview: C-Grid Connector Products
Description: SL Crimp Terminal, Series 70058, Female, 24-30 AWG, with 0.76µm Selective Gold (Au) Plated Contact, Reel
Replacement Part Number: <http://www.molex.com/molex/products/listview.jsp?channel=Products&sType=p&query=070058008370058-0083>

Documents:

[Drawing \(PDF\)](#) [Product Specification TS-70058-001-001 \(PDF\)](#)
[Product Specification PS-70058-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-70400-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	70058
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	C-Grid Connector Products
Packaging Alternative	16-02-0098 (Bag)
Product Name	CyClone, EXTreme Ten60Power, SL
Replacement Part Number	70058-0083
UPC	800753749139

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.073/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm ²	N/A

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	70058-0008
--------------------	------------

Reference - Drawing Numbers

Product Specification	PS-70058-001, PS-70400-001, TS-70058-001-001
Sales Drawing	700580001-SD-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[70058 Series](#)

Use With

SL Crimp Housing [70066](#) , [70450](#)

CyClone Connector [73099](#)

EXTreme Ten60Power [172510](#) ,
[172512](#)