



### Main

Range of product	Harmony XAC
Product or component type	Contact block
Component name	XENT
Electrical circuit type	Control circuit Power circuit
Contact block application	Emergency stop push-button
Contact block type	Single
Type of operator	Spring return
Product compatibility	XACD
Contacts type and composition	3 NC
Contact operation	Slow-break

### Complementary

Connections - terminals	Screw clamp terminals, connection capacity: 1 x 2.5 mm <sup>2</sup> with or without cable end Screw clamp terminals, connection capacity: 2 x 1.5 mm <sup>2</sup> with or without cable end
Mechanical durability	3000000 cycles
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	400 V (degree of pollution: 3) conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
Short-circuit protection	<= 6 A fuse protection by cartridge fuse type aM
Rated operational power in W	3000 W AC-23B at 400 V
Terminals description ISO n°1	(11-12)NC (21-22)NC (31-32)NC
Product weight	0.04 kg

### Environment

standards	EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14
ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
shock resistance	70 gn conforming to IEC 60068-2-27
overvoltage category	Class II conforming to IEC 61140

### Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.