

## XS1M08MB230

inductive sensor XS1 M8 - L50mm - stainless - Sn1mm - 24..240VAC/DC - cable 2m



### Main

Range of product	OsiSense XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XS1
Sensor design	Cylindrical M8
Size	50 mm
Body type	Fixed
Enclosure material	Stainless steel
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	1 mm
Discrete output function	1 NC
Electrical connection	Cable
Cable length	2 m
[Us] rated supply voltage	24...210 V DC 24...240 V AC
Switching capacity in mA	5...100 mA
IP degree of protection	IP67

### Complementary

ISO thread	M8 x 1
Detection face	Frontal
Detector flush mounting acceptance	Flush mountable
Material	Stainless steel
Front material	PPS
Output circuit type	AC/DC
Cable composition	2 x 0.11 mm <sup>2</sup>
Wire insulation material	PvR
Switching frequency	<= 25 Hz AC <= 3000 Hz DC
Marking	CE
Height	8 mm
Length	50 mm
Product weight	0.035 kg

### Environment

product certifications	CCC CSA UL
ambient air temperature for operation	-25...80 °C

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0843 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

---

Product environmental profile	Available
Product end of life instructions	Available

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---