

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0009508083**
Status: **Active**
Overview: KK® Interconnect System - Molex
Description: KK 3.96mm Crimp Terminal Housing, Friction Ramp, 8 Circuits, Natural

Documents:

3D Model Packaging Specification PK-41695-001-001 (PDF)
Drawing (PDF) RoHS Certificate of Compliance (PDF)
Product Specification PS-08-50-001 (PDF)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series 41695
 Application Power, Wire-to-Board
 Overview KK® Interconnect System - Molex
 Product Name KK 396
 UPC 800753692626

Physical

Breakaway No
 Circuits (maximum) 8
 Color - Resin Natural
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 2.814/g
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 3.96mm
 Polarized to Mating Part Yes
 Temperature Range - Operating See Product Specification

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number 41695-N-D8

Reference - Drawing Numbers

Packaging Specification PK-41695-001-001
 Product Specification PS-08-50-001
 Sales Drawing SD-41695-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

41695 Series

Mates With

KK 396 Header 41791 , 41792 , 41671 ,
41672 , 41661 , 41662

Use With

KK 396 Crimp Terminals, 2478 , 2578 , 6838
, 7258 , 45570