

**KEMET Part Number: C0603X102K3GECTU**  
(C0603X102K3GEC7867)

ESD SMD Comm COG, Ceramic, Electro Static Discharge, 1000 pF, 10%, 25 VDC, COG, SMD, MLCC, Temperature Stable, Electro Static Discharge, Class I, 0603



Dimensions	
<b>L</b>	1.6mm +/-0.17mm
<b>W</b>	0.8mm +/-0.15mm
<b>T</b>	0.8mm +/-0.15mm
<b>S</b>	0.58mm MIN
<b>B</b>	0.45mm +/-0.15mm

Packaging Specifications	
<b>Packaging:</b>	T&R, 180mm, Paper Tape
<b>Packaging Quantity:</b>	4000

General Information	
<b>Supplier:</b>	KEMET
<b>Series:</b>	ESD SMD Comm COG
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, Temperature Stable, Electro Static Discharge, Class I
<b>Features:</b>	Temperature Stable, Low ESR, Class I
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>Marking:</b>	No
<b>Chip Size:</b>	0603

Specifications	
<b>Capacitance:</b>	1000 pF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	25 VDC
<b>ESD Level per AEC-Q200:</b>	6,000 V ESD Level
<b>Dielectric Withstanding Voltage:</b>	62.5 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	COG
<b>Dissipation Factor:</b>	0.10% 1MHz 25C
<b>Aging Rate:</b>	0% Loss/Decade Hour
<b>Insulation Resistance:</b>	100 GOhms