



Meets ANSI/ESD S20.20 and Grounding standard ANSI/ESD S6.1

- A. 10mm (.395") snap socket (female) to ground work surface.
- B. Molded in black thermoplastic elastomer.
- C. Ring terminal, .200" ID, (#10).
- D. Extra ring terminal included for customizing length.
- E. The [09821](#) has a 1 megohm resistor between the snap and ground, with banana jacks at ground potential.
- F. The [09820](#) has no resistor between snap and ground, with banana jacks also at ground potential.
- G. Wire is autosplice crimped to secure it inside of the mold.
- H. High flex strand copper, 20 gauge, with PVC insulated jacket
[09821](#) - black insulation
[09820](#) - green insulation with yellow stripe
 OD = .100"
- I. Dual banana jacks at ground potential (.162" - .164" ± .002" ID).
- J. Desco and ground symbol molded into the plastic.
- K. Date coded to show month and year of manufacture. Arrow points to month of manufacture (12:00 = December), numerals indicate the year (03=2003).

Worksurface and two Wrist Straps can connect to Common Point Ground



Made in the United States of America



ITEM	LENGTH	CORD COLOR	RESISTOR
09820	10'	Green with Yellow Stripe	None
09821	10'	Black	1 Megohm

Specifications and procedures subject to change without notice.

COMMON POINT GROUND, WITH SNAP SOCKET (FEMALE), 10FT



DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com
 PHONE (909) 627-8178
 DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
 PHONE (781) 821-8370

DRAWING NUMBER
09820

DATE:
November 2018