

TECHNICAL DATA SHEET

PRO-POWER

Speaker Cable Model: CB17821

**RoHS
Compliant**

Design of cable:	
Inner conductor	30/0.24±0.004mm Strand Bare CopperØ1.52±0.1mm
Insulation	PE
Insulation Dia	Ø2.5±0.1mm
Insulation colour	Red/ Black/Green/White
Jacket	LSOH
Colour	Pink
Size	Ø7.5±0.2mm
Wall thickness	≈0.7mm
Printing	4 CORE 16AWG SPEAKER CABLE LSOH BATCH NO. Meter marking
Operational temperature	-10°C~70°C
Electric data at 20°C	
Conductor resistance	≤14.3Ω/km
Insulator resistance	≥200 MΩ*km
Testing Voltage	wire/wire 50Hz 1min=1500V
Packing	50meters on non-returnable reel

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

PRO-POWER