muRata Capacitor Data Sheet GCM0335C1E120GA16# "#" indicates a package specification code.

AEC-Q200 Cmax. Reflow RoHS REACH Power-train In Production

< List of part numbers with package codes >

Shape

GCM0335C1E120GA16D , GCM0335C1E120GA16W , GCM0335C1E120GA16J

ondpo		
L size	0.6 ±0.03mm	
W size	0.3 ±0.03mm	
T size	0.3 ±0.03mm	
External terminal width e	0.1 to 0.2mm	
Distance between external terminals g	0.2mm min.	
Size code in inch(mm)	0201 (0603M)	

Packaging	Specifications	Minimum quantity
D	φ180mm Paper taping	15000
J	φ330mm Paper taping	50000
W	φ180mm Paper taping (W8P1*) * Width : 8mm, Pocket pitch : 1mm	30000

Mass (typ.)	
1 piece	0.33mg
φ180mm Reel	118g

Specifications

Capacitance	12pF ±2%
Rated voltage	25Vdc
Temperature characteristics (complied standard)	C0G(EIA)
Temperature coefficient	0±30ppm/°C
Temperature range of temperature characteristics	25 to 125°C
Operating temperature range	-55 to 125°C

🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

References

