## muRata Capacitor Data Sheet GQM22M5C2H6R4DB01# "#" indicates a package specification code.

In Production Genera	125 ℃max.	High Q	Reflow OK	RoHS	REACH
----------------------	--------------	-----------	--------------	------	-------

< List of part numbers with package codes >

Shape

GQM22M5C2H6R4DB01L , GQM22M5C2H6R4DB01K

L size	2.8 ±0.5mm
W size	2.8 ±0.4mm
T size	1.15 ±0.2mm
External terminal width e	0.3mm min.
Distance between external terminals g	1.0mm min.
Size code in inch(mm)	1111 (2828M)

References
------------

Packaging	Specifications	Minimum quantity
L	φ180mm Embossed taping	1000
К	φ330mm Embossed taping	4000

Mass (typ.)		
1 piece	41mg	
φ180mm Reel	73g	

## Specifications

Capacitance	6.4pF ±0.5pF
Rated voltage	500Vdc
Temperature characteristics (complied standard)	C0G(EIA)
Temperature coefficient	0±30ppm/°C
Temperature range of temperature characteristics	25 to 125°C
Operating temperature range	-55 to 125°C

## 🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.