Power MOSFET

40 V, 0.4 m Ω , 553.8 A, Single N–Channel

Features

- Small Footprint (8x8 mm) for Compact Design
- Low R_{DS(on)} to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Typical Applications

- Power Tools, Battery Operated Vacuums
- UAV/Drones, Material Handling
- BMS/Storage, Home Automation

MAXIMUM RATINGS (T_J = 25° C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	40	V
Gate-to-Source Voltage			V _{GS}	±20	V
Continuous Drain	Steady State	T _C = 25°C	I _D	553.8	А
Current $R_{\theta JC}$ (Note 2)		$T_C = 100^{\circ}C$	I _D	394.8	А
Power Dissipation $R_{\theta JC}$ (Note 2)		T _C = 25°C	PD	244	W
		$T_C = 100^{\circ}C$	PD	122	W
Continuous Drain	Steady State	$T_A = 25^{\circ}C$	I _D	79.8	А
Current R _{θJA} (Notes 1, 2)		T _A = 100°C	I _D	56.4	А
Power Dissipation		$T_A = 25^{\circ}C$	PD	5.0	W
$R_{\theta JA}$ (Notes 1, 2)		T _A = 100°C	PD	2.5	W
Pulsed Drain Current	T _A = 25	°C, t _p = 10 μs	I _{DM}	900	А
Operating Junction and Storage Temperature			T _J , T _{stg}	–55 to + 175	°C
Source Current (Body Diode)			۱ _S	203.4	А
Single Pulse Drain–to–Source Avalanche Energy ($I_{L(pk)} = 70 A$)			E _{AS}	4454	mJ
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case - Steady State (Note 2)	$R_{\theta JC}$	0.61	°C/W
Junction-to-Ambient - Steady State (Note 2)	$R_{\theta JA}$	30.1	

1. Surface-mounted on FR4 board using a 1 in² pad size, 1 oz. Cu pad.


The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.



ON Semiconductor®


www.onsemi.com

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
40 V	0.4 mΩ @ 10 V	
40 V	0.64 mΩ @ 4.5 V	553.8 A





MARKING DIAGRAM



A = Assembly Location

- WL = 2-digit Wafer Lot Code
- Y = Year Code
- WW = Work Week Code

ORDERING INFORMATION


See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise specified)


Parameter	Symbol	Test Condition		Min	Тур	Max	Unit	
OFF CHARACTERISTICS								
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V_{GS} = 0 V, I _D = 250 μ A		40			V	
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} / T _J	$I_D = 250 \ \mu\text{A}, \text{ ref to } 25^\circ\text{C}$			8.86		mV/°C	
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V,$	$T_J = 25^{\circ}C$			10	μA	
		V _{DS} = 32 V	T _J = 125°C			250		
Gate-to-Source Leakage Current	I _{GSS}	V_{DS} = 0 V, V_{GS} = 20 V				100	nA	
ON CHARACTERISTICS (Note 3)								
Gate Threshold Voltage	V _{GS(TH)}	V_{GS} = V_{DS} , I_D = 250 μ A		1.0		2.5	V	
Negative Threshold Temperature Coefficient	V _{GS(TH)} /T _J	$I_D = 250 \ \mu A$, ref to $25^{\circ}C$			-6.24		mV/°C	
Drain-to-Source On Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 50 A		0.3	0.4		
		V _{GS} = 4.5 V	I _D = 50 A		0.45	0.64	mΩ	
Forward Transconductance	9 _{FS}	V _{DS} =5 V, I _D = 50 A			330		S	
Gate Resistance	R _G	T _A = 25°	C		1.0		Ω	
CHARGES, CAPACITANCES & GATE RESIS	TANCE							
Input Capacitance	C _{ISS}	V _{GS} = 0 V, f = 1 MHz, V _{DS} = 20 V			20600		pF	
Output Capacitance	C _{OSS}				9500			
Reverse Transfer Capacitance	C _{RSS}				709			
Total Gate Charge	Q _{G(TOT)}	V_{GS} = 4.5 V, V_{DS} = 20 V; I_{D} = 50 A			163		-	
Threshold Gate Charge	Q _{G(TH)}				29.8			
Gate-to-Source Charge	Q _{GS}				51		nC	
Gate-to-Drain Charge	Q _{GD}	V_{GS} = 10 V, V_{DS} = 20 V; I_{D} = 50 A			52.1			
Total Gate Charge	Q _{G(TOT)}				341			
Voltage Plateau	V _{GP}				2.7		V	
SWITCHING CHARACTERISTICS, $V_{GS} = 4.5$	V (Note 4)							
Turn–On Delay Time	t _{d(ON)}				110			
Rise Time	t _r	V _{GS} = 4.5 V, V _D	s = 20 V,		147		ns	
Turn–Off Delay Time	t _{d(OFF)}	$I_{\rm D} = 50 \rm A, R_{\rm G}$	= 6 Ω		217			
Fall Time	t _f	1			107		1	
SWITCHING CHARACTERISTICS, V_{GS} = 10	V (Note 4)							
Turn–On Delay Time	t _{d(ON)}				45.6			
Rise Time	t _r	V_{GS} = 10 V, V_{DS} = 20 V, I_{D} = 50 A, R_{G} = 6 Ω			39.8		ns	
Turn–Off Delay Time	t _{d(OFF)}				382			
Fall Time	t _f				96.4			
DRAIN-SOURCE DIODE CHARACTERISTIC	s							
Forward Diode Voltage	V _{SD}	V _{GS} = 0 V,	$T_J = 25^{\circ}C$		0.75	1.2		
		$I_{\rm S} = 50 {\rm A}$ $T_{\rm J} = 125^{\circ}{\rm C}$			0.58		V	
Reverse Recovery Time	t _{RR}	V _{GS} = 0 V, dIS/dt = 100 A/µs, I _S = 50 A			117			
Charge Time	t _a				87	-	ns	
Discharge Time	t _b				30			
Reverse Recovery Charge	Q _{RR}				336		nC	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 3. Pulse Test: pulse width $\leq 300 \ \mu$ s, duty cycle $\leq 2\%$. 4. Switching characteristics are independent of operating junction temperatures.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS





Figure 13. Thermal Characteristics

DEVICE ORDERING INFORMATION

Device	Marking	Package	Shipping [†]
NVMTS0D4N04CLTXG	0D4N04CL	POWER 88 (Pb–Free)	TBD / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS



ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for implantation in the human body. Should Buyer purchase or use ON Semiconductor hy such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated wi

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe. Middle East and Africa Technical Support:

ON Semiconductor Website: www.onsemi.com Order Literature: http://www.onsemi.com/orderlit

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

For additional information, please contact your local Sales Representative