



Request a Sample

Customer Specification PART NO. M4708

Construction

				Diameters (In)		
1) Component 1		40 X 1 COND				
a) Conductor		18 (16/30) AWG TC	18 (16/30) AWG TC		0.047	
b) Insulation		0.016" Wall, Nom. PV	0.016" Wall, Nom. PVC		0.079	
(1) Color Code		Alpha Wire Color Cod	Alpha Wire Color Code D			
Cond	Color	Cond	Color	Cond	Color	
1	BLACK	15	RED/BLACK	29	WHITE/BLACK/BROW N	
2	RED	16	WHITE/BLACK	30	WHITE/BLACK/ORAN GE	
3	WHITE	17	WHITE/RED	31	WHITE/BLACK/SLATE	
4	GREEN	18	WHITE/GREEN	32	WHITE/BLACK/VIOLE T	
5	ORANGE	19	WHITE/YELLOW	33	WHITE/BLACK/BLAC	
6	BLUE	20	WHITE/BLUE	34	WHITE/RED/BLACK	
7	BROWN	21	WHITE/BROWN	35	WHITE/RED/RED	
8	YELLOW	22	WHITE/ORANGE	36	WHITE/RED/GREEN	
9	VIOLET	23	WHITE/SLATE	37	WHITE/RED/BLUE	
10	SLATE	24	WHITE/VIOLET	38	WHITE/RED/BROWN	
11	PINK	25	WHITE/BLACK/RED	39	WHITE/RED/VIOLET	
12	TAN	26	WHITE/BLACK/GREE	40	WHITE/GREEN/BLAC	
13	RED/GREEN	27	WHITE/BLACK/YELL OW			
14	RED/YELLOW	28	WHITE/BLACK/BLUE			
2) Cable Assembly		40 Components Cabled				
a) Twists:		1.4 Twists/foot (min)				
b) Core Wrap		Clear Mylar Tape, 25% Overlap, Min.				
3) Shield:		Alum/Mylar Tape, 25% Overlap, Min.				
a) Foil Direction		Foil Facing In				
b) Drain Wire		18 (16/30) AWG TC				
4) Jacket		0.053" Wall, Nom.,PVC		0.690 (0.718 Max.)		
a) Color(s)		SLATE				
b) Ripcord		1 End 810 Denier Nylon				
c) Print		ALPHA WIRE-* P/N M4708 40C 18 AWG EXXXXXX SHIELDED 75C CMG (UL) C(UL) OR AWM 2464 CE ROHS * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]				

1) UL	AWM/STYLE 2464	80°C / 300 V _{RMS}
	СМС	75°C
2) CSA International	FT4	
	C(UL) TYPE CMG	75°C
3) CE:	EU Low Voltage Directive 2006/95/EC	

Environmental

1) CE: EU Directive 2011/65/EU(RoHS2), EU Directive 2015/863/EU (RoHS3):			
	This product complies with European Directive 2011/65/EU (RoHS Directive) of the European Parliament and of the Council of 8 June 2011 and the amending Directive 2015/863/EU of 4 June 2015. No Exemptions are required for RoHS Compliance on this item. Consult Alpha Wire's web site for RoHS C of C.		
2) REACH Regulation (EC 1907/2006):			
	This product does not contain Substances of Very High Concern (SVHC) listed on the European Union's REACH candidate list in excess of 0.1% mass of the item. For up-to-date information, please see Alpha's REACH SVHC Declaration.		
3) California Proposition 65:	Exempt from warning labels based on the Consent Judgment. Please see Alpha's CA Prop 65 Statement for more information.		

Properties

10001100				
Physical & Mechanical Properties				
1) Temperature Range	-20 to 80°C			
2) Bend Radius	10X Cable Diameter			
3) Pull Tension	515 Lbs, Maximum			
Electrical Properties	(For Engineering purposes only)			
1) Voltage Rating	300 V _{RMS}			
2) Capacitance	51 pf/ft @1 kHz, Nominal Conductor to Conductor			
3) Ground Capacitance	92 pf/ft @1 kHz, Nominal			
4) Inductance	0.18 μH/ft, Nominal			
5) Conductor DCR	7.2 Ω/1000ft @20°C, Nominal			
6) OA Shield DCR	5 Ω/1000ft @20°C, Nominal			

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	36 x 14 x 12 Continuous length
b) 500 FT	24 x 14 x 12 Continuous length
c) 100 FT	16 x 11 x 8 Continuous length
d) Bulk(Made-to-order)	
	[Spool dimensions may vary slightly]

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207 Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure their accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

ALPHA WIRE - CONFIDENTIAL AND PROPRIETARY

Notice to persons receiving this document and/or technical information. This document is confidential and is the exclusive property of ALPHA WIRE, and is merely on loan and subject to recall by ALPHA WIRE at any time. By taking possession of this document, the recipient acknowledges and agrees that this document cannot be used in any manner adverse to the interests of ALPHA WIRE, and that no portion of this document may be copied or otherwise reproduced without the prior written consent of ALPHA WIRE. In the case of conflicting contractual provisions, this notice shall govern the status of this document. ©2013 ALPHA WIRE - all rights reserved.



EU/China ROHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number: M4708

M4708, RoHS-Compliant Commencing With 11/1/2004 Production

Note: all colors and put-ups

This document certifies that the Alpha part number cited above is manufactured in accordance with Directive 2011/65/EU of the European Parliament, better known as the RoHS Directive (commonly known as RoHS 2), with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. This certification extends to amending Directive 2015/863/EU which expanded the list of restricted substances to 10 items (commonly known as RoHS 3) The reader is referred to these Directives for the specific definitions and extents of the Directives. **No Exemptions are required for RoHS Compliance on this item**. Additionally, Alpha certifies that the listed part number is in compliance with China RoHS "Marking for Control of Pollution by Electronic Information Products" standard SJ/T 11364-2014.

Substance	Maximum Control Value	
Lead	0.1% by weight (1000 ppm)	
Mercury	0.1% by weight (1000 ppm)	
Cadmium	0.01% by weight (100 ppm)	
Hexavalent Chromium	0.1% by weight (1000 ppm)	
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)	
Polybrominated Diphenyl Ethers (PBDE) ,		
Including Deca-BDE	0.1% by weight (1000 ppm)	
Bis(2-ethylhexyl) phthalate (DEHP)	0.1% by weight (1000 ppm)	
Butyl benzyl phthalate (BBP)	0.1% by weight (1000 ppm)	
Dibutyl phthalate (DBP)	0.1% by weight (1000 ppm)	
Diisobutyl phthalate (DIBP)	0.1% by weight (1000 ppm)	

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire:

Dave Watson, Director of Engineering & QA

Alpha Wire

711 Lidgerwood Ave. Elizabeth, NJ 07207 Tel: 1-908-925-8000 9/11/2019