

# 18V COMBI DRILL BL LXT

## DHP485Z

DHP485 is a cordless hammer driver drill powered by 18V Li-ion battery and has been developed based on the model DHP459.



### TECHNICAL SPECIFICATIONS

Capacity in Steel	13 mm
Capacity in Wood	38 mm
Chuck Capacity	1.5 - 13 mm
No Load Speed (Hi)	0 - 1,900 rpm
No Load Speed (Lo)	0 - 500 rpm
Blows per Minute (Hi) - ipm	0 - 28,500 ipm
Blows per Minute (Lo) - ipm	0 - 7,500 ipm
Capacity in Masonry	13 mm
Voltage	18 v
Torque Settings	21 + drill
Battery Type	Lithium-ion
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	82 dB(A)
Noise sound power	93 dB(A)
Noise K factor	3 dB(A)
Body only machine	✓
Net weight	1.5 - 1.8 kg
Battery Quantity (5.0ah)	0

### USER BENEFITS

- Brushless motor
- Forward / reverse rotation
- Single sleeve keyless chuck allows for easy bit installation/removal by one hand.
- Electric brake
- 2 mechanical gears.
- Variable speed control by trigger
- Best possible ergonomic handle for drill-driver applications.
- LED job light

[Link to product - www.makita.com](http://www.makita.com)



# RELATED PRODUCTS

(Recom

## ■ OTHER