



Kvaser D-sub 9 pin 120 Ohm termination adapter

EAN: 73-30130-00801-4

Kvaser D-sub 9 pin 120 Ohm termination adapter is a CAN adaptor with a 9-pin male D-Sub connector at one end and a 9-pin female D-Sub socket at the other. Between CAN High (pin 7) and CAN Low (pin 2) there is a built-in 120 Ohm CAN terminating resistor.

This adapter provides quick and easy termination to any Kvaser high-speed CAN product. The Kvaser CAN termination adapter is used when there is a need to terminate a CAN node without internal termination or when no CAN node is connected to the bus. The Kvaser D-sub 9 pin 120 Ohm termination adapter has a 9-pin male D-Sub plug connector and a 9-pin female D-Sub socket. A 120 ohm terminating resistor sits between pins 2 and 7.

TECHNICAL DATA - KVASER D-SUB 9 PIN 120 OHM TERMINATION ADAPTER	
SOUND	N/A
MAXIMUM BITRATE (KBPS)	N/A
WIDTH (MM)	N/A
PIN COUNT	N/A
CURRENT CONSUMPTION	N/A
OPERATING TEMPERATURE RANGE (C)	-30.00 to 85.00
TIMESTAMP RESOLUTION (US)	N/A
IP CLASS	
SILENT MODE	No
OPERATING SYSTEM	Win 10,Win Vista,Linux,Win 8,Win 7,Win XP
EMBEDDED SCRIPT	No
ON-BOARD TX BUFFER	No
ON-BOARD BUFFER	N/A
CERTIFICATIONS	CE,RoHS
MAXIMUM BITRATE (KBPS)	N/A
CURRENT CONSUMPTION	
API, FREE	N/A
CAN FD	No
CLOCK SYNC	No
CERTIFICATIONS	CE,RoHS
NETWORK CHANNEL(S)	
ERROR FRAME GENERATION	No
GALVANIC ISOLATION	N/A
ERROR COUNTERS READING	N/A
GALVANIC ISOLATION	No
MSGRATE RX MAX	N/A



## Kvaser D-sub 9 pin 120 Ohm termination adapter

NETWORK CHANNEL(S)		
PRODUCT GROUP		N/A
CASING MATERIAL		N/A
PIN COUNT		N/A
CASING MATERIAL		N/A
API, LICENCED		
ON-BOARD TX BUFFER		N/A
MSGRATE RX MAX		N/A
PC INTERFACE		Cable
CAN FD		No
CB BOARD		No
PRODUCT GROUPS		Accessory
ERROR FRAME GENERATION		N/A
ERROR COUNTERS READING		No
SOUND		No
RUGGED		No
RUGGED		N/A
# OF CAN CHANNELS		0
TIMESTAMP RESOLUTION (US)		N/A
DATABASE DBC SUPPORT		No
HEIGHT (MM)		N/A
IP CLASS		N/A
STATUS		Active
OPERATING TEMPERATURE RANGE (C)		-30.00 to 85.00
HEIGHT (MM)		N/A
MINIMUM BITRATE (KBPS)		N/A
CLOCK SYNC		N/A
CONNECTOR		DSUB 9

Kvaser  
 Aminogatan 25 A SE 431 53 Mölndal SWEDEN  
 Kvaser Europe AB  
 Telephone: +46 31 886344  
 Email: sales@kvaser.com  
<https://www.kvaser.com/>



## Kvaser D-sub 9 pin 120 Ohm termination adapter

API, FREE	
API, LICENCED	None
LENGTH (MM)	N/A
MINIMUM BITRATE (KBPS)	N/A
PC INTERFACE	Cable
OPERATING SYSTEM	Win 10,Win Vista,Linux,Win 8,Win 7,Win XP
PRODUCT GROUPS	Accessory
ERROR FRAME DETECTION	No
PLAY BACK LOG FILE	No
ERROR FRAME DETECTION	N/A
MSGRATE TX MAX	N/A
SILENT MODE	N/A
ON-BOARD RX BUFFER	N/A
CB BOARD	No
CASING MATERIAL	N/A
# OF CAN CHANNELS	0
WEIGHT (G)	N/A
STATUS	Active
WEIGHT (G)	N/A
ON-BOARD BUFFER	No
ON-BOARD RX BUFFER	No
CONNECTOR	DSUB 9
MSGRATE TX MAX	N/A
EMBEDDED SCRIPT	No

The information herein is subject to change without notice

Kvaser  
 Aminogatan 25 A SE 431 53 Mölndal SWEDEN  
 Kvaser Europe AB  
 Telephone: +46 31 886344  
 Email: sales@kvaser.com  
<https://www.kvaser.com/>