

Master cable - SAC-14P-30,0-PUR/M16FR - 1622093


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Master cable, application: Sensor/actuator box Metal, number of slots: 10, number of positions: 14, slot assignment: single, status display: No; master cable connection: M16 plug connection, PUR/PVC, cable length: 30 m, shielding: no



Key Commercial Data

| | |
|--------------------------------------|---|
| Packing unit | 1 pc |
| Minimum order quantity | 2 pc |
| GTIN |  4 055626 009926 |
| GTIN | 4055626009926 |
| Weight per Piece (excluding packing) | 3,641.000 g |
| Custom tariff number | 85444290 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data


Environmental Product Compliance

| | |
|------------|---|
| | Lead 7439-92-1 |
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

Drawings

Master cable - SAC-14P-30,0-PUR/M16FR - 1622093


Circuit diagram



Contact assignment of the M16 socket

Master cable - SAC-14P-30,0-PUR/M16FR - 1622093

Cable cross section



PUR/PVC black [PUR]

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 5.1 | 27061801 |
| eCl@ss 6.0 | 27279200 |
| eCl@ss 7.0 | 27279218 |
| eCl@ss 8.0 | 27279218 |
| eCl@ss 9.0 | 27060311 |

ETIM

| | |
|----------|----------|
| ETIM 5.0 | EC001855 |
| ETIM 6.0 | EC001855 |
| ETIM 7.0 | EC001855 |

Master cable - SAC-14P-30,0-PUR/M16FR - 1622093

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 13.2 | 31251501 |
| UNSPSC 19.0 | 31251501 |
| UNSPSC 20.0 | 31251501 |
| UNSPSC 21.0 | 31251501 |

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|---|---------|
| EAC |  | B.00767 |
|-----|---|---------|
