


## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Hazardous substances label, Card, red/white, pre-printed, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, diameter: 0 mm, lettering field size: 13 x 13 mm, Number of individual labels: 50

### Your advantages

- ✔ Stick-on hazardous substances labels, color preprinted, without symbol
- ✔ Suitable for indoor and outdoor use
- ✔ The markers conform to the GHS international standard
- ✔ High adhesive strength
- ✔ High temperature resistance



### Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 786614
GTIN	4046356786614
Weight per Piece (excluding packing)	6.430 g
Custom tariff number	39199080
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Length (b)	13 mm
Width (a)	13 mm
Height (c)	13 mm
Diameter	0.00 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Technical data

#### General

Color	red/white
Type	Diamond
Components	Silicone-free
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	50
Marking mounting type	adhesive

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Classifications

#### eCl@ss

eCl@ss 10.0.1	40200202
eCl@ss 4.0	40200100
eCl@ss 4.1	40200100
eCl@ss 5.0	40200100
eCl@ss 5.1	27371300
eCl@ss 6.0	40200100
eCl@ss 7.0	40200103
eCl@ss 8.0	40200202
eCl@ss 9.0	40200202

#### ETIM

ETIM 3.0	EC000712
ETIM 4.0	EC002498
ETIM 5.0	EC001777
ETIM 6.0	EC001777
ETIM 7.0	EC001777

#### UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	55121718
UNSPSC 18.0	55121718
UNSPSC 19.0	55121718
UNSPSC 20.0	55121718
UNSPSC 21.0	55121718

## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

#### Accessories

##### Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110-TC - 0801371



Ink ribbon, for THERMOMARK CARD for printing product groups UCT..., US..., and UM..., width: 110 mm, color: black

---

### Labeled systems marker

Pipeline markers - PML-T101 (26X280)R CUS - 1014249



Pipeline markers, can be ordered: by line, green, labeled according to customer specifications: Water, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

---

Pipeline markers - PML-T101 (52X560)R CUS - 1014250

Pipeline markers, can be ordered: by line, green, labeled according to customer specifications: Water, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



---

Pipeline markers - PML-T102 (26X280)R CUS - 1014251



Pipeline markers, can be ordered: by line, red, labeled according to customer specifications: Steam, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

---

Pipeline markers - PML-T102 (52X560)R CUS - 1014252

Pipeline markers, can be ordered: by line, red, labeled according to customer specifications: Steam, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

Pipeline markers - PML-T103 (26X280)R CUS - 1014253



Pipeline markers, can be ordered: by line, gray, labeled according to customer specifications: Air, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T103 (52X560)R CUS - 1014254



Pipeline markers, can be ordered: by line, gray, labeled according to customer specifications: Air, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T104 (26X280)R CUS - 1014255



Pipeline markers, can be ordered: by line, yellow/red, labeled according to customer specifications: flammable gases, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T104 (52X560)R CUS - 1014256



Pipeline markers, can be ordered: by line, yellow/red, labeled according to customer specifications: flammable gases, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T105 (26X280)R CUS - 1014257



Pipeline markers, can be ordered: by line, yellow/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

#### Pipeline markers - PML-T105 (52X560)R CUS - 1014258

Pipeline markers, can be ordered: by line, yellow/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



#### Pipeline markers - PML-T106 (26X280)R CUS - 1014259



Pipeline markers, can be ordered: by line, orange, labeled according to customer specifications: Acids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

#### Pipeline markers - PML-T106 (52X560)R CUS - 1014260

Pipeline markers, can be ordered: by line, orange, labeled according to customer specifications: Acids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



#### Pipeline markers - PML-T107 (26X280)R CUS - 1014261



Pipeline markers, can be ordered: by line, violet, labeled according to customer specifications: Alkalis, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

#### Pipeline markers - PML-T107 (52X560)R CUS - 1014262

Pipeline markers, can be ordered: by line, violet, labeled according to customer specifications: Alkalis, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

Pipeline markers - PML-T108 (26X280)R CUS - 1014263



Pipeline markers, can be ordered: by line, brown/red, labeled according to customer specifications: flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T108 (52X560)R CUS - 1014264



Pipeline markers, can be ordered: by line, brown/red, labeled according to customer specifications: flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T109 (26X280)R CUS - 1014265



Pipeline markers, can be ordered: by line, brown/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

Pipeline markers - PML-T109 (52X560)R CUS - 1014266



Pipeline markers, can be ordered: by line, brown/black, labeled according to customer specifications: Non-flammable liquids, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm

Pipeline markers - PML-T110 (26X280)R CUS - 1014267



Pipeline markers, can be ordered: by line, blue, labeled according to customer specifications: Oxygen, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm

## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

#### Pipeline markers - PML-T110 (52X560)R CUS - 1014268

Pipeline markers, can be ordered: by line, blue, labeled according to customer specifications: Oxygen, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm



---

### System marking

#### Pipeline markers - PML-T101 (26X280)R - 1014229



Pipeline markers, Roll, green, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

---

#### Pipeline markers - PML-T101 (52X560)R - 1014230

Pipeline markers, Roll, green, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



---

#### Pipeline markers - PML-T102 (26X280)R - 1014231



Pipeline markers, Roll, red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

---

#### Pipeline markers - PML-T102 (52X560)R - 1014232

Pipeline markers, Roll, red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

#### Pipeline markers - PML-T103 (26X280)R - 1014233



Pipeline markers, Roll, gray, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

#### Pipeline markers - PML-T103 (52X560)R - 1014234



Pipeline markers, Roll, gray, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

#### Pipeline markers - PML-T104 (26X280)R - 1014235



Pipeline markers, Roll, yellow/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

#### Pipeline markers - PML-T104 (52X560)R - 1014236



Pipeline markers, Roll, yellow/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

#### Pipeline markers - PML-T105 (26X280)R - 1014237



Pipeline markers, Roll, yellow/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250



## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

#### Pipeline markers - PML-T105 (52X560)R - 1014238

Pipeline markers, Roll, yellow/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



#### Pipeline markers - PML-T106 (26X280)R - 1014239



Pipeline markers, Roll, orange, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

#### Pipeline markers - PML-T106 (52X560)R - 1014240

Pipeline markers, Roll, orange, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



#### Pipeline markers - PML-T107 (26X280)R - 1014241



Pipeline markers, Roll, violet, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

#### Pipeline markers - PML-T107 (52X560)R - 1014242

Pipeline markers, Roll, violet, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

#### Pipeline markers - PML-T108 (26X280)R - 1014243



Pipeline markers, Roll, brown/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

#### Pipeline markers - PML-T108 (52X560)R - 1014244



Pipeline markers, Roll, brown/red, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

#### Pipeline markers - PML-T109 (26X280)R - 1014245



Pipeline markers, Roll, brown/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

#### Pipeline markers - PML-T109 (52X560)R - 1014246



Pipeline markers, Roll, brown/black, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250

#### Pipeline markers - PML-T110 (26X280)R - 1014247



Pipeline markers, Roll, blue, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 26 x 280 mm, Number of individual labels: 250

## Hazardous substances label - US-PML-GHS100 (13X13) - 1014287

### Accessories

Pipeline markers - PML-T110 (52X560)R - 1014248

Pipeline markers, Roll, blue, pre-printed, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: adhesive, diameter: 0 mm, lettering field size: 52 x 560 mm, Number of individual labels: 250



---

Phoenix Contact 2019 © - all rights reserved  
<http://www.phoenixcontact.com>