

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022152126](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK 254 PC Board Connector, Right-Angle, End-to-End Stackable, 2.54µm Tin (Sn), 12 Circuits

Documents:

[3D Model](#) [Packaging Specification PK-44646-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-10-07-001 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Receptacles
 Series [4455](#)
 Application Board-to-Board, Signal
 Overview [KK® Interconnect System - Molex](#)
 Product Name KK 254
 UPC 800753752238


Physical

Circuits (Loaded) 12
 Circuits (maximum) 12
 Color - Resin Natural (White)
 Flammability 94V-0
 Glow-Wire Capable No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part No
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 1.256/g
 Number of Rows 1
 Orientation Right Angle
 PC Tail Length 3.35mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 2.54mm
 Pitch - Termination Interface 2.54mm
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Polarized to PCB Yes
 Temperature Range - Operating See Product Specification
 Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 2.5A
 Grounding to PCB No
 Voltage - Maximum 500V

Solder Process Data



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[4455 Series](#)

Mates With

KK Header [4094](#) , [42376](#) , [42375](#) , [42377](#) ,
[4030](#) , [171856](#) , [171857](#)

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	A-4455-AZ12A(P909)
--------------------	--------------------

Reference - Drawing Numbers

Packaging Specification	PK-44646-001-001
Product Specification	PS-10-07-001
Sales Drawing	SDA-4455-001, SDA-4455-002

This document was generated on 03/25/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION