

CFL535G, TDR2010 and TDR2050

Advanced Dual Channel TDR



- **600 V CAT IV Input Protection filter built in**
- **Step and Pulse TDR selections**
- **Distance Dependant Gain**
- **Test straight from the box**
- **Trace Tagging**
- **2ns pulse width**
- **Designed for use on all metallic paired cables**

DESCRIPTION

The Megger® CFL535G, TDR2010 and TDR2050 are state of the art, dual channel, high resolution, compact Time Domain Reflectometers with a color screen for locating faults on paired metallic cables.

All TDRs in this series have a minimum resolution of 0.1 m / 0.3 ft and a 20 km / 65 kft maximum range depending on the velocity factor selected and the cable type.

Various output impedances are available (CFL535G and TDR2010: 25, 50, 75, 100, 125 ohm + AUTO. TDR2050: 25, 50, 75, 100, 140 ohm + AUTO) and an auto impedance matching feature. The velocity factor can be set between 0.2 and 0.99 to meet any cable test requirements.

FEATURES AND BENEFITS

The instruments have a large, high resolution, color, WVGA display with easy set up features. Directional control buttons, together with soft keys, provide intuitive and easy operation for the user.

An AUTO selection option ensures that the most effective parameters are selected depending on the range required, aiding rapid diagnosis of the TDR trace. The ability to manually override the auto function allows fine tuning to enable identification of hard to determine faults.

Dual trace and dual cursor capabilities allow full flexibility, giving the operator full control and instant indication of distance between two points.

A trace comparison feature also allows close examination between trace conditions. Extra high resolution together with a white-light backlight, user definable color schemes give the graphical display a vibrance, aiding the user in identifying key events on the trace.

600 V CAT IV input protection

TDR2050 is the first TDR in this class to include a built-in 600 V input protection filter. The ability to connect to potentially live circuits means a more flexible instrument suited for a wider range of applications.

Trace Storage

100 internal trace memories provide for the storage and recall of test results. The traces can be recalled to the display for analysis or compared with an active display to aid in fault location.

Alternatively the stored results can be downloaded to a computer, via the USB port, using the TraceXpert software and USB lead provided.

Step TDR function

The Dead Zone effect of a standard pulse TDR can mask near end faults and make them undetectable. The addition of a step function on the TDR2050 eliminates this problem.

Step TDR technology means that the signal is injected at full strength and stays there until a disturbance is detected. This makes step TDR technology perfect for detecting near end faults that standard pulse TDRs can miss.

Distance dependant gain

This feature, built into the TDR2050, eliminates the drop off of signal attenuation on longer lines by gradually increasing the gain along the returned signal, enabling a more even representation of the relative attenuation at all points along the trace.

Fault identification

Megger's own built-in AutoFind mode allows for speedy identification of faults. One press of the AutoFind key automatically adjusts the range and gain, and positions the cursor to the first major event on the cable. Press the AutoFind key again and the cursor will jump to the next detected disturbance.

FindEnd function

TDR2050 also incorporates a FindEnd function, which allows the user to automatically search the trace to identify the end of the cable under test. This is useful in situations where a fast cable length measurement is required.

For those who wish to maintain manual control, manual operation allows full override access to refine the response for easy fault identification.

Color schemes

The very different light conditions that could be present when using the TDR2050, combined with the limitations of eye conditions such as color blindness, makes the addition of set color schemes in the instrument extremely important.

TDR2010 and TDR2050 have 6 additional set color schemes on top of the Default and Outdoor schemes included on other Megger TDRs. There are also 2 custom slots where the user can specify their own scheme by setting up to 7 screen elements to their own choice of color.

Trace Tagging

TDR2010 and TDR2050 also incorporate a Trace Tagging feature which allows the user to add a name to saved traces. This could be the circuit ID, building name or any other identifying text the user wishes to save with the trace.

A text string of up to 32 alphanumeric characters can be stored against each trace and this can consist of upper case letters including accents.

TraceXpert PC software

The CFL535G, TDR2010 and TDR2050 come complete with the Megger TraceXpert software which gives full control over downloading, reporting and uploading of saved trace results. Designed around a database and programmed for ease of use and simplicity, TraceXpert offers the ideal application for all your data processing requirements.

Models

The series is available in 3 models.

CFL535G

A fully featured high resolution TDR with backlit color display and powered by Li-ion rechargeable battery batteries. This model comes complete with 2 pairs of mini-clip Test Leads.

TDR2010

The same as the CFL535G but with Trace Tagging and additional Color Scheme selection.

TDR2050

The same as TDR2010 but with the addition of 600 V CAT IV rating, Step, DDG and FindEnd functions.

BENEFITS (MODEL DEPENDENT)

- Backlit graphics color LCD (800x480)
- Adjustable display contrast
- Resolution to 0.1 m
- AutoFind guide to potential fault location
- 100 trace on board memory
- USB connection to PC allowing upload and download of traces
- "TraceXpert" PC software analysis tool
- For use on Telecom TNV-3 circuit, or 150 V CAT IV power circuits (CFL535G and TDR2010 only)
- For use on power circuits to 600 V CAT IV (TDR2050 only)
- Power blocking filter built-in
- Environmental protection to IP54
- Selectable output impedance
CFL535G and 2010: 25, 50, 75, 100, 125 ohm + AUTO.
TDR2050: 25, 50, 75, 100, 140 ohm + AUTO.
- 2ns pulse for near end fault location
- AUTO option selecting gain and pulse for each range
- AUTO option matches output impedance to cable
- Display distance in metres or feet
- Li-ion rechargeable battery (12 hours typical life)

SPECIFICATION

Except where otherwise stated, this specification applies at an ambient temperature of 20°C

GENERAL

Range

Up to 20000 m with a minimum resolution of 0.1 m
(Maximum range dependent on cable type)

m	ft	ns
10	30	125
25	80	250
50	160	500
100	320	1000
250	800	2500
500	1600	5000
1000	3200	10000
2500	8000	25000
5000	16000	50000
10000	32500	100000
20000	65000	200000

Accuracy

±1% of range ±1 pixel at 0.67 VF

[Note - The measurement accuracy is for the indicated cursor position only and is conditional on the velocity factor being correct.

Resolution

1% of range.

Input protection

This instrument complies with IEC61010-1 to protect the user in the event of connection to live systems. TDR2050 is rated at 600 V CAT IV while all other models are rated at 150 V CAT IV. TDR2050 is specifically designed to allow use on energized systems up to the rated voltage. All other models are designed for use on de-energized systems and fused leads must be used if the potential voltage between terminals could exceed 300 V.

Output pulse

Up to 20 volts peak to peak into open circuit. Pulse widths determined by range, cable and model used.

Gain

Set for each range with user selectable steps (in Manual operating mode).

Velocity factor

Variable from 0.2 to 0.99 in steps of 0.01.

TX null

Automatic

Trace Tagging - 32 characters chosen from upper case letters including accents

Color schemes - Default, Outdoor, Custom

Step TDR - Eliminates the Dead Zone effect

DDG - Available in ranges 1000 m and above in 0.5 dB steps

Cable Impedance CFL535G and TDR2010: 25, 50, 75, 100, 125 ohm + AUTO. TDR2050: - 25, 50, 75, 100, 140 ohm + AUTO.

Power down

User programmable auto power off timer 1, 5, 10 mins or never.

Battery

Li-ion rechargeable battery.

Battery charge time

6 hours at 0 °C to 40 °C.

Battery life

12 hours typical.

Safety

These instruments comply with IEC61010-1 for connections to live systems up to 150 V CAT IV or 300 V CAT III (CFL535G and TDR2010 only).

TDR2050 is rated at 600 V CAT IV. Fused leads must be used if the voltage between terminals exceeds 300 V.

Compliant with EN60950-1, EN61010-1, UN38.3 and EN62133.

EMC

Complies with Electromagnetic Compatibility Specifications (Light industrial) BS EN 61326-1, with a minimum performance of 'B' for all immunity tests.

MECHANICAL

IP rating

The instrument is designed for use indoors or outdoors and is rated to IP54.

Case

ABS.

Dimensions

290 mm (11.4 in) x 190 mm (7.5 inches) x 55 mm (2.2 inches)

Weight

1.7kg (3.8lbs)

Connectors

Four 4mm-safety terminals and two F connectors. Other standard push on adapters will fit. F connectors not available on TDR2050.

Test lead

CFL535G and TDR2010 - 1.5 meters long consisting of 2 x 4 mm shrouded connector to miniature crocodile clips

CFL535GP and TDR2050 - 1.5 meter fused leads.

Display

800 x 480 pixel color graphics LCD, viewable in external environments.

Color Schemes

Selectable

CFL535G x2

TDR2010, TDR2050 x8

Custom

CFL535G x1

TDR2010, TDR2050 x2

Backlight

Permanent backlight with all color schemes (adjustable brightness)

ENVIRONMENTAL

Operating temperature range and humidity

-15 °C to +50 °C (5 °F to 122 °F)

Storage temperature range and humidity

-20 °C to 70 °C (-4 °F to 158 °F)

ORDERING INFORMATION

Description	Order Code	Description	Order Code
Ordering information		Included accessories	
TDR2050 Power TDR	1005-023	TDR2050 Lead sets	
TDR2010 Dual Channel Comms	1007-078	Retractable sheath fused test lead (2 pairs)	1006-511
CLF535G Dual channel	1007-069	CFL535G and TDR2010 Lead sets	
		Dual miniature clip test lead set	6231-654
		TDR2010 US and CFL535G	
		Dual Comms Lead set with Bed of Nails Clips	6231-655
		Download kit	1003-353
		Carry case	1003-217
		AC-DC charger	1003-352
		User guide CD	
		Optional accessories	
		Miniature clip test lead set (1 pair)	6231-652
		Split conductor fused test lead set (1 pair)	1002-015
		Replacement battery	1002-552
		Terminal adaptor kit	1003-218
		AC power lead - US	25970-002
		Red and black probes and clips - for use with all Megger TDR Fused Test Leads.	1002-491
		Retractable sheath fused test lead (1 pair)	1006-511

SALES OFFICE
Megger USA -
Valley Forge Corporate Center
2621 Van Buren Avenue, Norristown,
Pennsylvania, 19403, USA
T. 1-610 676 8500
F. 1-610-676-8610

CFL535G--TDR2010--TDR2050_DS_us_V09
www.megger.com
ISO 9001
The word 'Megger' is a registered trademark

