

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1728320001](#)  
**Status:** **Active**  
**Overview:** [NeoPress Mezzanine System](#)  
**Description:** NeoPress High-Speed Mezzanine Receptacle, 3.50mm Pitch, 6x14, 84 Triads (252 Circuits), 13.50mm Connector Height, 0.76µm Gold (Au) Plating

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-173358-0001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-172801-0001-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Application Specification AS-172801-0001-001 (PDF)</a>	

**Agency Certification**

UL E29179

**Application tooling part link**

Application Tooling Part Link	62203-1310
Application Tooling Part Link	62203-1320
Application Tooling Part Link	62203-1410

**General**

Product Family	PCB Receptacles
Series	<a href="#">172832</a>
Application	Board-to-Board, Signal
Electrical Model	No
Overview	<a href="#">NeoPress Mezzanine System</a>
Product Literature Order No	987651-3181
Product Name	NeoPress
UPC	889056200561

**Physical**

Circuits (Loaded)	252
Circuits (maximum)	252
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	Liquid Crystal Polymer
Net Weight	17.462/g
Number of Rows	6
Orientation	Vertical
PC Tail Length	1.38mm
PCB Locator	No
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	3.50mm
Plating min - Mating	0.762µm
Plating min - Termination	1.270µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	None



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[172832](#) Series

**Mates With**

[172801-0001](#) NeoPress 3.50mm Pitch Plug

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
NeoPress Receptacle Assembly Press-In Tool for 6-Pair by 14 Column Assemblies	<a href="#">622031310</a>
NeoPress Removal Tool for NeoPress Plugs and Receptacles	<a href="#">622031320</a>
NeoPress Removal Tool for NeoPress	<a href="#">622031410</a>

Stackable	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

Plugs and Receptacles
--------------------------

**Electrical**

Current - Maximum per Contact	1.0A
Grounding to PCB	No
Voltage - Maximum	30V AC (RMS)

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info****Reference - Drawing Numbers**

Application Specification	AS-172801-0001-001
Electrical Model Document	1728017002-000, 1728017005-000
Packaging Specification	PK-173358-0001-001
Product Specification	PS-172801-0001-001
Sales Drawing	1728320002-000
Signal Integrity Report	1728017002REV1-000

This document was generated on 04/23/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**