

M12 slim angled female D-cod 4-pol



Part number	21 03 881 4405
Specification	M12 slim angled female D-cod 4-pol
HARTING eCatalogue	https://b2b.harting.com/21038814405

Identification

Category	Connector
Series	Circular connectors M12
Identification	M12 Slim Design
Element	Cable connector
Specification	Angled

Version

Termination method	Crimp termination
Gender	Female
Locking type	Screw locking
Shielding	Shielded
Number of contacts	4
Coding	D-coding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm ²
Conductor cross-section	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	250 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	> 10 ⁸ Ω



Pushing Performance

Technical characteristics

Contact resistance	≤10 mΩ
Ambient temperature	-40 ... +85 °C
Tightening torque	0.6 Nm
Wrench size	A/F 15 Knurled screw / knurled nut
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 when mated IP67 when mated
Cable diameter	5.7 ... 8.8 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Overvoltage category	III
Isolation group	I (600 ≤ CTI)

Material properties

Material (insert)	LCP
Material (hood/housing)	Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61076-2-101
----------------	-----------------

Commercial data

Packaging size	10
Net weight	68.5 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440102 Circular connector (for field assembly)