



**EXCELTA**<sup>®</sup>  
SINCE 1957

Data Sheet: 7241E

Excelta 7241E

Description: -★★★★★- Maximum Flush – Medium Round Head Cutter  
Cutting Capacity: .005" - .045" (.13MM – 1.13mm) Soft Copper Wire  
Shape: Medium Round  
Cut Type: Maximum Flush  
Material: Carbon Steel with Molded ESD Safe grips (10<sup>8</sup> ohms/sq)  
Tip Size: .38" (9.5 mm)  
Overall Length: 4.5" (112.5 mm)  
Body Width: 0.42" (10.5 mm)  
Body Height: 0.25" (6.88 mm)  
Made in USA

The Lazer Line<sup>®</sup> medium oval head cutters have a larger frame than the SLIM LINE series allowing them to cut a larger diameter lead/wire. They are made of AISI 52100 carbon tool steel with induction hardened cutting blades to RHC 63-65. The CNC machining allows the joint surfaces to be perfect to allow for long life. These tools include dual leaf springs for a very smooth action. The grips are molded and are static dissipative (10<sup>8</sup> ohms/sq).



**EXCELTA**<sup>®</sup>  
SINCE 1957

T: 805-694-2169 | F: 805-686-9005