

Main

Product or component type	Sinus filter
Range compatibility	Altivar 61 Altivar 61Q Altivar 71 Altivar Process ATV600 Altivar 71Q Altivar Process ATV900
Product specific application	Output filter
[In] rated current	600 A
Thermal losses	2370 W at 100 Hz
Product compatibility	ATV61HC31N4 ATV61QC25N4 ATV61QC31N4 ATV71HC25N4 ATV71HC28N4 ATV71QC25N4 ATV61QC40N4 ATV71QC31N4 ATV71QC40N4 ATV930 variable speed drive wall mount - 250 kW, 380...480 V ATV930 variable speed drive wall mount - 315 kW, 380...480 V ATV61HC40N4 ATV71HC31N4 ATV71HC40N4 ATV61HC25N4
Switching frequency	4...8 kHz
Output frequency	<= 100 Hz
Maximum permissible voltage	500 V AC

Complementary

Electrical connection	Bare wires, Ø = 14 mm
Voltage drop at rated load	< 10 %
Max current	1.5 x nominal current for 60 s
Product weight	260 kg

Environment


IP degree of protection	IP00
-------------------------	------

Environmental characteristic	3B1 conforming to IEC 721-3-3 3C2 conforming to IEC 721-3-3 3S1 conforming to IEC 721-3-3
Pollution degree	2 conforming to EN 50178
Vibration resistance	1 gn (f = 13...200 Hz) conforming to IEC 60068-2 1.5 mm peak to peak (f = 3...13 Hz) conforming to IEC 60068-2
Shock resistance	15 gn for 11 ms conforming to IEC 60068-2-27
Relative humidity	0...95 %
Ambient air temperature for operation	> 40...50 °C with current derating 1.5 % per °C -10...40 °C without current derating
Ambient air temperature for storage	-40...65 °C
Operating altitude	<= 1000 m without current derating 1000...3000 m with current derating 1 % per 100 m

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions



Dimensions in mm

a	b	c	G	H	Ø	Ø1
480	710	370	430	258	13 x 18	14

Dimensions in in.

a	b	c	G	H	Ø	Ø1
18.90	27.95	14.57	16.93	10.16	0.51 x 0.71	0.55

Mounting Recommendations

