

MAX505S Black

- Waterproof and dustproof IP67 certified
- Mil Specs (STANAG 4280, DEF STAN 81-41)
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Holes for double padlocking
- Holes for shoulder strap
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free

Body and handle: polypropylene copolymer
Latches: nylon
Pins: nylon + 30% fiberglass
O-ring: polymer

COLOURS: Black, orange, sahara

EXTERNAL DIMENSIONS: 555 x 428 x H211 mm (21.85 x 16.85 x H8.31 inch)

INTERNAL DIMENSIONS: 500 x 350 x H194 mm (19.69 x 13.78 x H7.64 inch)

LID-BOTTOM DEPTH: 58 + 136 mm (2.28 + 5.36 inch)

WEIGHT WITH FOAM: 4.38 kg – 9.66 lbs.

CAPACITY: 25kg – 55 lbs.

CARTON DIMENSIONS: 570 x 450 x 235mm – 22.44 x 17.72 x 9.25 inch

PCS PER CARTON: 1

WEIGHT OF THE FULL CARTON WITH FOAMS: 5.22 kg – 11.51 lbs.

MOLDING: injection molding

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: IP67, DEF STAN 81-41, STANAG 4280

COSTUMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foams, pouch, padded dividers, padded shoulder strap

